

Diamond Bars (shank diameter 3mm)

Stock 954 Items

5-1193

Prices displayed include 8% tax.

For Micro Grinders, see p. 5-242 to 268


TRUSCO Stock 38,650 Items

Diamond Internal Bar (cylinder with round end)



- Features**
- Because the tip has a rounded shape, it is suitable for use such as opening holes and removing burr from small holes.
- Origin**
- Japan


(T3-710M)




(T3-715M)



(T3-720M)



(T3-725M)



(T3-730M)



(T3-740M)



(T3-750M)



Warning
• When working, please wear protective equipment such as safety hat and safety glasses.

Order Unit: 1 Piece

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Grain Size (#)	Cutting Diameter x Blade Length x Shaft Diameter x Total Length (mm)	Length Excl. Head (mm)	Max Working Rotation Speed (rpm)	SPQ (piece)	Weight (g)
767-3728	T3-710M	¥1,126	¥1,390	140/170	1.0 x 6 x 3 x 45	5	80000	1	2.0
767-3744	T3-715M	¥1,126	¥1,390	140/170	1.5 x 6 x 3 x 45	5	80000	1	2.1
767-3761	T3-720M	¥1,126	¥1,390	140/170	2.0 x 12 x 3 x 45	6	80000	1	1.9
767-3787	T3-725M	¥1,353	¥1,670	140/170	2.5 x 12 x 3 x 45	6	80000	1	2.1
767-3809	T3-730M	¥1,353	¥1,670	140/170	3.0 x 12 x 3 x 45	-	80000	1	2.4
767-3825	T3-740M	¥1,548	¥1,910	140/170	4.0 x 10 x 3 x 45	-	60000	1	2.7
767-3841	T3-750M	¥1,612	¥1,990	140/170	5.0 x 10 x 3 x 45	-	55000	1	3.2

Contact us: 0120-509-849 <http://www.orange-book.com/>

TRUSCO Stock 38,650 Items





Disc Type Diamond Bar



- Features**
- A high precision shank by integral processing.
 - Realized a more flat disc by using synthetic diamond.
 - We adopt stainless steel which is rust resistant.
 - More rigidity than the mandrel type.
- Use**
- Groove process.
 - Cutting process.
 - Surface Processing
 - Chamfering process.
 - Burring processing.
- Materials**
- Stainless Steel (SUS303)
 - Synthetic Diamond
- Origin**
- Japan



Warning
• Please use safety glasses/dust mask.
• Please use with low cutting pressure.



Order Unit: 1 Piece

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Grain Size (#)	Cutting Diameter x Blade Length x Shaft Diameter x Total Length (mm)	Max Working Rotation Speed (rpm)	SPQ (piece)	Weight (g)
352-3179	T3-167DM-05	¥3,009	¥3,250	140	7.0 x 0.5 x 3 x 45	40000	1	2.4
352-3225	T3-167DM-10	¥3,009	¥3,250	140	7.0 x 1.0 x 3 x 45	40000	1	2.6
352-3195	T3-169DM-07	¥3,286	¥3,550	140	9.0 x 0.7 x 3 x 45	40000	1	2.6
352-3187	T3-169DM-14	¥3,286	¥3,550	140	9.0 x 1.4 x 3 x 45	40000	1	2.9
352-3241	T3-171DM-07	¥3,703	¥4,000	140	11.0 x 0.7 x 3 x 45	30000	1	2.8
352-3268	T3-171DM-14	¥3,703	¥4,000	140	11.0 x 1.4 x 3 x 45	30000	1	3.2
352-3292	T3-173DM-07	¥4,212	¥4,550	140	13.0 x 0.7 x 3 x 40	30000	1	2.7
352-3306	T3-173DM-14	¥4,212	¥4,550	140	13.0 x 1.4 x 3 x 40	30000	1	3.4
352-3314	T3-175DM-10	¥4,906	¥5,300	140	15.0 x 1.0 x 3 x 40	30000	1	3.3

Contact us: 0120-509-849 <http://www.orange-book.com/>

Abrasives

Grinding Wheels

Disk Papers

Papers for Double Action Sander

Nylon Discs

Urethane Discs

Felt Discs

Diamond Wheels

Grinding Wheels

Dressers

Flap Wheels

Nylon Wheel with Shaft

Shank Mounted Felt Wheels with Shaft

Bands

Shank Mounted Stones

Carbide Bars

Diamond Bars

CBN Bars

Files

Diamond Files

Grinding Stones

Abrasives

Sheet Sanding Papers

Abrasive Belts

Cup Brushes

Wheel Brushes with Shank

Hand Brushes