

Disc Papers (mini type)

For Disc Grinders, see p. 5-209 to 226

The number next to the logo mark indicates items in stock for each brand.



Stock 38,650 Items

Disc Paper "GP Top Mini"



- Features**
- A flap disc exclusive for 50mm air-operated tools.
 - Has 5- to 6-fold the long life of offset type whetstones and does not create polishing burns.
- Use**
- Welding bead removal and spatter removal.
 - Burr removal.
- Specs**
- Maximum working peripheral velocity: 52.3m/s (3140m/min)
 - **Outer diameter: 50mm**
- Materials**
- Alumina Abrasive
- Origin**
- Japan



GP5010A series

Order Unit: 1 Box

Order Code	Item No.	Price (per box)	MSRP (per box)	Grain Size (#)	Outer Diameter x Blade Length x Hole Diameter (mm)	Max Working Rotation Speed (rpm)	Blade Number (sheet)	Q'ty Per Box (sheet)	SPQ (box)	Weight (g/box)
360-9677	GP5010A-40	¥2,511	¥3,100	40	50 x 12 x 9.6	20000	36	5	5	62
360-9685	GP5010A-60	¥2,511	¥3,100	60	50 x 12 x 9.6	20000	36	5	5	54
360-9693	GP5010A-80	¥2,511	¥3,100	80	50 x 12 x 9.6	20000	36	5	5	50
360-9707	GP5010A-100	¥2,511	¥3,100	100	50 x 12 x 9.6	20000	36	5	5	48
360-9715	GP5010A-120	¥2,511	¥3,100	120	50 x 12 x 9.6	20000	36	5	5	45
360-9723	GP5010A-150	¥2,511	¥3,100	150	50 x 12 x 9.6	20000	36	5	5	44
360-9731	GP5010A-180	¥2,511	¥3,100	180	50 x 12 x 9.6	20000	36	5	5	43
360-9740	GP5010A-240	¥2,511	¥3,100	240	50 x 12 x 9.6	20000	36	5	5	43
360-9758	GP5010A-320	¥2,511	¥3,100	320	50 x 12 x 9.6	20000	36	5	5	43
360-9766	GP5010A-400	¥2,511	¥3,100	400	50 x 12 x 9.6	20000	36	5	5	43

TRUSCO NAKAYAMA CORPORATION

Estimated Unit Price per Sheet
¥502

Contact us: 0120-509-849 <http://www.orange-book.com/>



Stock 38,650 Items

Disc Paper "GP Top Mini"



- Features**
- Rich in particle size variation, it is a versatile type that covers from rough finishing to finish polishing. Prevents grinding burn which is the difficult point of elastic grinding wheel, has high grinding amount and a long life of 5 to 6 times of flexible grindstone.
- Use**
- Optimum for removal of spot welding spatter of automobiles, home electric appliance product etc., especially for polishing of molding die.
 - For general metal.
- Specs**
- Max Working Peripheral Velocity: 60.7m/s (3642m/min)
 - **Outer Diameter: 58mm**
- Materials**
- Alumina Abrasive
- Origin**
- Japan



GP5810:60

Order Unit: 1 Box

Order Code	Item No.	OP	Price (per box)	MSRP (per box)	Grain Size (#)	Outer Diameter x Blade Length x Hole Diameter (mm)	Max Working Rotation Speed (rpm)	Blade Number (sheet)	Q'ty Per Box (sheet)	SPQ (box)	Weight (g/box)
118-1408	GP5810	40	¥2,754	¥3,400	40	58 x 15 x 9.6	20000	48	5	20	133
118-1416	GP5810	60	¥2,754	¥3,400	60	58 x 15 x 9.6	20000	48	5	20	123
118-1424	GP5810	80	¥2,754	¥3,400	80	58 x 15 x 9.6	20000	48	5	20	119
118-1432	GP5810	100	¥2,754	¥3,400	100	58 x 15 x 9.6	20000	48	5	20	114
118-1441	GP5810	120	¥2,754	¥3,400	120	58 x 15 x 9.6	20000	48	5	20	105
118-1459	GP5810	150	¥2,754	¥3,400	150	58 x 15 x 9.6	20000	48	5	20	105
118-1467	GP5810	180	¥2,754	¥3,400	180	58 x 15 x 9.6	20000	48	5	20	105
118-1475	GP5810	240	¥2,754	¥3,400	240	58 x 15 x 9.6	20000	48	5	20	105
118-1483	GP5810	320	¥2,754	¥3,400	320	58 x 15 x 9.6	20000	48	5	20	105
118-1491	GP5810	400	¥2,754	¥3,400	400	58 x 15 x 9.6	20000	48	5	20	105

TRUSCO NAKAYAMA CORPORATION

Estimated Unit Price per Sheet
¥551

Contact us: 0120-509-849 <http://www.orange-book.com/>



Stock 1,066 Items

"Mild Techno A"



- Features**
- Adopting a base plate that is much smaller than the disc diameter enables free warping and play of the polishing cloths.
 - The polishing cloths fit perfectly on curved surfaces and irregularly shaped surfaces. Since air-cooling and heat radiation works in the gaps between the round polishing cloths, there is almost no scorching or clogging.
- Use**
- Polishing prior to plating. • Rust removal prior to painting. • Polishing of stainless steel and iron.
- Specs**
- Maximum working peripheral velocity: 79m/s (4740m/min)
 - **Outer diameter: 50mm**
- Materials**
- Alumina Abrasive
- Origin**
- Japan



MT5010-A series

Order Unit: 20 Sheets

Order Code	Item No.	Price (per sheet)	MSRP (per sheet)	Q'ty Per Pack (sheet)	Grain Size (#)	Outer Diameter x Blade Length x Hole Diameter (mm)	Max Working Rotation Speed (rpm)	Blade Number (sheet)	Weight (g)
397-2348	MT5010-A-40	¥544*	¥620*	20	40	50 x 10 x 10	15000	36	8
397-2364	MT5010-A-60	¥544*	¥620*	20	60	50 x 10 x 10	15000	36	8
397-2381	MT5010-A-80	¥544*	¥620*	20	80	50 x 10 x 10	15000	36	8
397-2283	MT5010-A-100	¥544*	¥620*	20	100	50 x 12 x 10	15000	36	8
397-2291	MT5010-A-120	¥544*	¥620*	20	120	50 x 12 x 10	15000	36	8
397-2305	MT5010-A-150	¥544*	¥620*	20	150	50 x 12 x 10	15000	36	8
397-2313	MT5010-A-180	¥544*	¥620*	20	180	50 x 12 x 10	15000	36	8
397-2321	MT5010-A-240	¥544*	¥620*	20	240	50 x 12 x 10	15000	36	8
397-2330	MT5010-A-320	¥544*	¥620*	20	320	50 x 12 x 10	15000	36	8
397-2356	MT5010-A-400	¥544*	¥620*	20	400	50 x 12 x 10	15000	36	8
397-2372	MT5010-A-600	¥544*	¥620*	20	600	50 x 12 x 10	15000	36	8

ICHIGUCHI CORPORATION

Contact us: 0774-94-9033 <http://www.ichiguchi.co.jp/>