

# For Desktops

## DDR4 288-PIN Unbuffered DIMM

	512Mx8 (9pcs) (CL15)	4GB	TS512MLH64V1H
DDR4-2133	512Mx8 (18pcs) (CL15)	8GB	TS1GLH64V1H
	1024Mx8 (18pcs) (CL15)	16GB	TS2GLH64V1B

## DDR3 240-PIN Unbuffered DIMM

	256Mx8 (8pcs) (CL11)	2GB	TS256MLK64V6N
	256Mx8 (8pcs) (CL11) 0.74"	2GB	TS256MLK64V6NL
	256Mx8 (8pcs) (CL11) 1.35V	2GB	TS256MLK64W6N
	256Mx8 (16pcs) (CL11) 1.35V	4GB	TS512MLK64W6N
DDR3-1600	512Mx8 (8pcs) (CL11)	4GB	TS512MLK64V6H
	512Mx8 (8pcs) (CL11) 1.35V	4GB	TS512MLK64W6H
	512Mx8 (16pcs) (CL11)	8GB	TS1GLK64V6H
	512Mx8 (16pcs) (CL11) 1.35V	8GB	TS1GLK64W6H
	1020X8 (16pcs) (CL11) 1.35V	16GB	TS2GLK64W6G
	128Mx8 (8pcs) (CL9)	1GB	TS128MLK64V3U
	128Mx8 (8pcs) (CL9)	1GB	TS128MLK64V3U-I*
	128Mx8 (8pcs) (CL9) 0.74"	1GB	TS128MLK64V3UL
	128Mx8 (16pcs) (CL9)	2GB	TS256MLK64V3U
	128Mx8 (16pcs) (CL9) 0.74"	2GB	TS256MLK64V3UL
DDR3-1333	256Mx8 (8pcs) (CL9)	2GB	TS256MLK64V3N
	256Mx8 (8pcs) (CL9)	2GB	TS256MLK64V3N-I*
	256Mx8 (8pcs) (CL9) 0.74"	2GB	TS256MLK64V3NL
	256Mx8 (16pcs) (CL9)	4GB	TS512MLK64V3N
	256Mx8 (16pcs) (CL9)	4GB	TS512MLK64V3N-I*
	256Mx8 (16pcs) (CL9) 0.74"	4GB	TS512MLK64V3NL
	512Mx8 (8pcs) (CL9)	4GB	TS512MLK64V3H
	512Mx8 (16pcs) (CL9)	8GB	TS1GLK64V3H
DDR3-1066	128Mx8 (8pcs) (CL7)	1GB	TS128MLK64V1U
	128Mx8 (16pcs) (CL7)	2GB	TS256MLK64V1U

## DDR3 240-PIN JetRam Series

	256Mx8 (8pcs) (CL11)	2GB	JM1600KLN-2G
DDR3-1600	512Mx8 (8pcs) (CL11)	4GB	JM1600KLH-4G
	512Mx8 (32pcs) (CL11)	16GB	JM1600KLH-16GK(8GBx2)
DDR3-1333	256Mx8 (8pcs) (CL9)	2GB	JM1333KLN-2G
	512Mx8 (8pcs) (CL9)	4GB	JM1333KLH-4G

## DDR2 240-PIN Unbuffered DIMM

	64Mx8 (8pcs) (CL5)	512MB	TS64MLQ64V8J
DDR2-800	64Mx8 (16pcs) (CL5)	1GB	TS128MLQ64V8J
	128Mx8 (8pcs) (CL6)	1GB	TS128MLQ64V8U
	128Mx8 (16pcs) (CL6)	2GB	TS256MLQ64V8U
	64Mx8 (8pcs) (CL5)	512MB	TS64MLQ64V6J
DDR2-667	64Mx8 (16pcs) (CL5)	1GB	TS128MLQ64V6J
	128Mx8 (8pcs) (CL5)	1GB	TS128MLQ64V6U
	128Mx8 (16pcs) (CL5)	2GB	TS256MLQ64V6U
	32Mx16 (4pcs) (CL4)	256MB	TS32MLQ64V5M
DDR2-533	64Mx8 (8pcs) (CL4)	512MB	TS64MLQ64V5J
	64Mx8 (16pcs) (CL4)	1GB	TS128MLQ64V5J
	128Mx8 (16pcs) (CL4)	2GB	TS256MLQ64V5U
DDR2-400	64Mx8 (8pcs) (CL3)	512MB	TS64MLQ64V4J

## DDR2 240-PIN JetRam Series

DDR2-800	128Mx8 (8pcs) (CL6)	1GB	JM800QLU-1G
	128Mx8 (16pcs) (CL6)	2GB	JM800QLU-2G
DDR2-667	128Mx64(8pcs) (CL5)	1GB	JM667QLU-1G
	128Mx8 (16pcs) (CL5)	2GB	JM667QLU-2G

## DDR 184-PIN JetRam Series

DDR-400	32Mx8 (16pcs) (CL2.5)	512MB	JM366D643A-50
	64Mx8 (16pcs) (CL3)	1GB	JM388D643A-5L

## DDR 184-PIN Unbuffered DIMM

	32Mx8 (8pcs) (CL2.5)	256MB	TS32MLD64V4F
	32Mx8 (8pcs) (CL3)	256MB	TS32MLD64V4F3
DDR-400	32Mx8 (16pcs) (CL2.5)	512MB	TS64MLD64V4F
	64Mx8 (8pcs) (CL3)	512MB	TS64MLD64V4J
	32Mx8 (16pcs) (CL3)	512MB	TS64MLD64V4F3
	64Mx8 (16pcs) (CL3)	1GB	TS128MLD64V4J
	16Mx16 (4pcs)	128MB	TS16MLD64V3G
DDR-333	32Mx8 (8pcs)	256MB	TS32MLD64V3F5
	32Mx8 (16pcs)	512MB	TS64MLD64V3F5
	64Mx8 (8pcs)	512MB	TS64MLD64V3J
	64Mx8 (16pcs)	1GB	TS128MLD64V3J
	32Mx8 (8pcs)	256MB	TS32MLD64V6F5
DDR-266	32Mx8 (16pcs)	512MB	TS64MLD64V6F5
	64Mx8 (8pcs)	512MB	TS64MLD64V6J
	64Mx8 (16pcs)	1GB	TS128MLD64V6J



Scan QR Code for more information

# For Notebooks

## DDR4 260-PIN SO-DIMM

	512Mx8 (8pcs) (CL15)	4GB	TS512MSH64V1H
DDR4-2133	512Mx8 (16pcs) (CL15)	8GB	TS1GSH64V1H
	1024Mx8 (16pcs) (CL15)	16GB	TS2GSH64V1B

## DDR3 204-PIN SO-DIMM

	256Mx8 (8pcs) (CL11)	2GB	TS256MSK64V6N
	256Mx8 (8pcs) (CL11) 1.35V	2GB	TS256MSK64W6N
	256Mx8 (8pcs) (CL11) 1.35V	2GB	TS256MSK64W6N-I*
	256Mx16 (8pcs) (CL11) 1.35V	2GB	TS256MSK64W6X
DDR3-1600	256Mx8 (16pcs) (CL11)	4GB	TS512MSK64V6N
	256Mx8 (8pcs) (CL11) 1.35V	4GB	TS512MSK64W6H
	512Mx8 (8pcs) (CL11)	4GB	TS512MSK64W6H-I*
	128Mx8 (8pcs) (CL11) 1.35V	4GB	TS512MSK64W6H
	512Mx8 (16pcs) (CL11) 1.35V	8GB	TS1GSK64W6H
	512Mx8 (16pcs) (CL11)	8GB	TS1GSK64V6H
	512Mx8 (16pcs) (CL11)	8GB	TS1GSK64V6H-I*
	1024x8 (16pcs) (CL11)	16GB	TS2GSK64W6Q
	512Mx8 (16pcs) (CL11)	16GB	TS1600KWSH-16GK
	128Mx8 (8pcs) (CL9)	1GB	TS128MSK64V3U
	128Mx8 (8pcs) (CL9)	1GB	TS128MSK64V3U-I*
	256Mx8 (8pcs) (CL9) 1.35V	2GB	TS256MSK64W3N
	128Mx8 (16pcs) (CL9)	2GB	TS256MSK64V3U
	256Mx8 (8pcs) (CL9)	2GB	TS256MSK64V3N
DDR3-1333	256Mx8 (8pcs) (CL9)	2GB	TS256MSK64V3N-I*
	256Mx8 (16pcs) (CL9)	4GB	TS512MSK64V3N
	256Mx8 (16pcs) (CL9)	4GB	TS512MSK64V3N-I*
	256Mx8 (16pcs) (CL9) 1.35V	4GB	TS512MSK64W3N
	512Mx8 (8pcs) (CL9)	4GB	TS512MSK64V3H
	512Mx8 (16pcs) (CL9)	8GB	TS1GSK64V3H
	512Mx8 (16pcs) (CL9)	8GB	TS1GSK64V3H-I*
	128Mx8 (8pcs) (CL7)	1GB	TS128MSK64V1U
DDR3-1066	128Mx8 (16pcs) (CL7)	2GB	TS256MSK64V1U
	256Mx8 (8pcs) (CL7)	2GB	TS256MSK64V1N
	256Mx8 (16pcs) (CL7)	4GB	TS512MSK64V1N

## DDR3 204-PIN JetRam Series

	256Mx8 (16pcs) (CL11)	4GB	JM1600KSN-4G
DDR3-1600	512Mx8 (8pcs) (CL11)	4GB	JM1600KSH-4G
	512Mx8 (16pcs) (CL11)	16GB	JM1600KSH-16GK(8GBx2)
	128Mx8 (8pcs) (CL9)	1GB	JM1333KSU-1G
DDR3-1333	128Mx8 (16pcs) (CL9)	2GB	JM1333KSU-2G
	256Mx8 (16pcs) (CL9)	4GB	JM1333KSN-4G

## DDR2 200-PIN SO-DIMM

	64Mx16 (4pcs) (CL6)	512MB	TS64MSQ64V8Q
DDR2-800	64Mx16 (8pcs) (CL6)	1GB	TS128MSQ64V8W
	128Mx8 (8pcs) (CL6)	1GB	TS128MSQ64V8U
	128Mx8 (8pcs) (CL6)	1GB	TS128MSQ64V8U-I*
	128Mx8 (16pcs) (CL6)	2GB	TS256MSQ64V8U
	128Mx8 (16pcs) (CL6)	2GB	TS256MSQ64V8U-I*
	32Mx16 (4pcs) (CL5)	256MB	TS32MSQ64V6M
	32Mx16 (8pcs) (CL5)	512MB	TS64MSQ64V6M
	64Mx8 (8pcs) (CL5)	512MB	TS64MSQ64V6J
	64Mx8 (8pcs) (CL5)	512MB	TS64MSQ64V6J-I*
DDR2-667	64Mx8 (8pcs) (CL3)	512MB	TS64MSQ64V6Q
	64Mx8 (16pcs) (CL5)	1GB	TS128MSQ64V6J
	128Mx8 (8pcs) (CL5)	1GB	TS128MSQ64V6U
	128Mx8 (8pcs) (CL5)	1GB	TS128MSQ64V6U-I*
	128Mx8 (16pcs) (CL5)	2GB	TS256MSQ64V6U
	128Mx8 (16pcs) (CL5)	2GB	TS256MSQ64V6U-I*
	32Mx16 (8pcs) (CL4)	512MB	TS64MSQ64V5M
	64Mx8 (8pcs) (CL4)	512MB	TS64MSQ64V5J
DDR2-533	64Mx8 (16pcs) (CL4)	1GB	TS128MSQ64V5J
	128Mx8 (8pcs) (CL4)	1GB	TS128MSQ64V5U
	128Mx8 (8pcs) (CL4)	1GB	TS128MSQ64V5U-I*
	128Mx8 (16pcs) (CL4)	2GB	TS256MSQ64V5U
	128Mx8 (16pcs) (CL4)	2GB	TS256MSQ64V5U-I*

## DDR2 200-PIN JetRam Series

DDR2-800	128Mx8 (16pcs) (CL6)	2GB	JM800QSU-2G
DDR2-667	128Mx8 (8pcs) (CL5)	1GB	JM667QSU-1G
	128Mx8 (16pcs) (CL5)	2GB	JM667QSU-2G

## DDR 200-PIN SO-DIMM

	32Mx8 (8pcs) (CL3)	256MB	TS32MSD64V4F3
DDR-400	64Mx8 (8pcs) (CL3)	512MB	TS64MSD64V4J
	64Mx8 (8pcs) (CL3)	512MB	TS64MSD64V4J-I*
	64Mx8 (16pcs) (CL3)	1GB	TS128MSD64V4A
	64Mx8 (8pcs) (CL3)	1GB	TS128MSD64V3G
	16Mx16 (4pcs)	128MB	TS16MSD64V3G
	16Mx16 (8pcs)	256MB	TS32MSD64V3G
DDR-333	32Mx16 (4pcs)	256MB	TS32MSD64V3M
	32Mx8 (8pcs)	256MB	TS32MSD64V3F5
	64Mx8 (8pcs)	512MB	TS64MSD64V3J
	32Mx16 (8pcs)	512MB	TS64MSD64V3M
	64Mx8 (16pcs)	1GB	TS128MSD64V3A
DDR-266	16Mx16 (4pcs)	128MB	TS16MSD64V6G
	32Mx8 (8pcs)	256MB	TS32MSD64V6F5



Scan QR Code for more information