



サイズ $\phi 0.3 \sim \phi 2$

UTDSX



対応被削材表 (☆○○の順に推奨)

被 削 材																
一般構造 圧延鋼 SS400	炭素鋼 S45C S55C	合金鋼 SK / SCM SUS	プリハードン鋼 NAK HPM	焼入れ鋼			鋳鉄	アルミ合金	グラファイト	銅	樹脂	ガラス入り樹脂	チタン合金	超耐熱合金	超硬合金	硬脆材
				~55HRC	~60HRC	~70HRC										
○	○	○	○	45HRC 以上の高硬度材加工については別途ご相談ください。			○	◎		○			○	○		

合計 35 型番

単位 (mm)

型番	直径 ϕD	溝長 l	全長 L	シャック径 ϕd	定価 (¥)
UTDSX 2030-015	0.3	1.5	38	3	3,470
UTDSX 2035-018	0.35	1.8	38	3	3,860
UTDSX 2040-020	0.4	2	38	3	3,470
UTDSX 2045-023	0.45	2.3	38	3	3,860
UTDSX 2050-025	0.5	2.5	38	3	3,860
UTDSX 2055-028	0.55	2.8	38	3	3,070
UTDSX 2060-030	0.6	3	38	3	2,670
UTDSX 2065-033	0.65	3.3	38	3	3,070
UTDSX 2070-035	0.7	3.5	38	3	2,670
UTDSX 2075-038	0.75	3.8	38	3	3,070
UTDSX 2080-040	0.8	4	38	3	2,670
UTDSX 2085-043	0.85	4.3	38	3	3,070
UTDSX 2090-045	0.9	4.5	38	3	2,670
UTDSX 2095-048	0.95	4.8	38	3	3,070
UTDSX 2100-050	1	5	38	3	2,480
UTDSX 2105-053	1.05	5.3	38	3	2,480
UTDSX 2110-055	1.1	5.5	38	3	2,480
UTDSX 2115-058	1.15	5.8	38	3	2,480
UTDSX 2120-060	1.2	6	38	3	2,480
UTDSX 2125-063	1.25	6.3	38	3	2,480
UTDSX 2130-065	1.3	6.5	38	3	2,480
UTDSX 2135-068	1.35	6.8	38	3	2,480
UTDSX 2140-070	1.4	7	38	3	2,480
UTDSX 2145-073	1.45	7.3	38	3	2,480
UTDSX 2150-075	1.5	7.5	38	3	2,480
UTDSX 2155-078	1.55	7.8	38	3	2,480
UTDSX 2160-080	1.6	8	38	3	2,480
UTDSX 2165-083	1.65	8.3	38	3	2,670
UTDSX 2170-085	1.7	8.5	38	3	2,670
UTDSX 2175-088	1.75	8.8	38	3	2,670
UTDSX 2180-090	1.8	9	38	3	2,670
UTDSX 2185-093	1.85	9.3	38	3	2,670
UTDSX 2190-095	1.9	9.5	38	3	2,670
UTDSX 2195-098	1.95	9.8	38	3	2,670
UTDSX 2200-100	2	10	38	3	2,670