




TOTAKU DUCT-D

Item No.21101-



Features.

- Lightness and flexibility enable labor-saving.
- Easy to cut and install, easy for installation.

Applications.

- For exhausts and air supplying of equipment and machinery.
- For aerial equipment.
- Additionally, for dust collection and air supplying exhaust

STANDARD DIMENSIONS & PROPERTIES

Nominal diameter	I.D.	O.D.	Pitch	Weight (reference)	L/coil	Allowable pressure (at room temperature)		Allowable decompression power (at room temperature)		Allowable bending radius	
						MPa	kgf/cm ²	kPa	mmHg		mm
32	1¼	32.4	38.6	7.5	255	50	0.06	0.6	-66.0	-495	32
38	1½	37.3	44.5	7.9	360	50	0.06	0.6	-66.0	-495	38
50	2	50.8	59.8	11.0	545	50	0.05	0.5	-6.0	-495	50
65	2½	64.0	73.2	11.1	685	30	0.04	0.4	-66.0	-495	65
75	3	76.5	85.9	11.7	825	30	0.04	0.4	-33.0	-248	75
90	3½	90.0	100.0	12.0	1050	30	0.03	0.3	-33.0	-248	90
100	4	103.0	113.0	12.0	1245	30	0.03	0.3	-22.5	-169	100
125	5	127.3	137.3	12.1	1445	20	0.02	0.2	-12.0	-90	125
150	6	151.4	162.0	13.5	1830	20	0.02	0.2	-10.0	-75	150
175	7	176.6	187.8	13.7	2170	20	0.01	0.1	-8.0	-60	175
200	8	205.0	216.8	14.3	2760	20	0.01	0.1	-6.5	-49	200
250	10	252.1	263.9	13.9	3290	10	0.01	0.1	-4.0	-30	250
300	12	303.0	316.0	15.7	4090	10	0.01	0.1	-2.5	-19	300




Installation cuffs

The size is ø32~ø200

(Note) Theø175 cuffs are rubber (EPDM), and size of others are soft PVC

TOTAKU DUCT-FR

Item No.21149-



Features.

- With reinforcing fiber, strong in growth and excellent bending resistance.
- Matches new equipment by ivory white coloring which changes images of vinyl ducts.

Applications.

- For exhausts and air supplying of equipment and machinery
- For air conditioning equipment
- Additionally, for dust collection and air supplying exhaust

Installation cuffs: made of the Soft-PVC

STANDARD DIMENSIONS & PROPERTIES

Nominal diameter	I.D.	O.D.	Pitch	Weight (reference)	L/coil	Allowable pressure (at room temperature)		Allowable decompression power (at room temperature)		Allowable bending radius	Installation cuffs	
						MPa	kgf/cm ²	kPa	mmHg			mm
32	1¼	32.0	40.0	8.5	300	50	0.10	1.0	-49.0	-368	32	Yes
38	1½	38.0	46.2	9.0	400	50	0.10	1.0	-49.0	-368	38	Yes
50	2	50.6	61.0	10.0	665	30	0.08	0.8	-49.0	-368	50	Yes
65	2½	62.4	72.6	12.0	730	30	0.07	0.7	-49.0	-368	65	Yes
75	3	76.4	86.8	15.1	795	30	0.07	0.7	-40.0	-300	75	Yes
90	3½	88.9	99.3	15.1	950	30	0.07	0.7	-29.0	-218	90	Yes
100	4	101.6	113.0	16.4	1135	30	0.07	0.7	-21.5	-161	100	Yes
125	5	125.9	139.3	21.0	1640	20	0.04	0.4	-20.0	-150	125	Yes
150	6	152.4	166.0	20.0	2000	20	0.03	0.3	-20.0	-150	150	Yes
200	8	203.7	217.5	22.5	2760	20	0.02	0.2	-11.0	-83	200	Yes