



TOTAKU DUCT-AS

Item No.21133- □



STANDARD DIMENSIONS & PROPERTIES

Nominal diameter	I.D.	O.D.	Pitch	Weight (reference)	L/coil	Allowable pressure (at room temperature)		Allowable decompression power (at room temperature)	Allowable bending radius	
						MPa	kgf/cm ²			
32	1¼	32.4	38.6	8.4	220	50	0.06	0.6	-66.0 {-495}	32
38	1½	37.3	44.5	9.2	295	50	0.06	0.6	-66.0 {-495}	38
50	2	50.6	60.2	10.0	560	30	0.05	0.5	-66.0 {-495}	50
65	2½	62.4	72.0	12.0	615	30	0.04	0.4	-66.0 {-495}	65
75	3	76.4	86.4	13.0	775	30	0.04	0.4	-33.0 {-248}	75
※90	3½	88.9	100.1	13.5	945	30	0.03	0.3	-33.0 {-248}	90
100	4	101.6	112.2	15.0	1145	30	0.03	0.3	-21.5 {-161}	100
125	5	125.9	137.7	21.0	1350	20	0.02	0.2	-20.0 {-150}	125
150	6	152.4	164.8	20.0	1620	20	0.02	0.2	-14.5 {-109}	150

The size of ※ mark will be built to order as a custom-made item
For any more information, please inquire of us.

Mounting method

Please use SPIRAL WIRE BAND (ø32-ø150, P52) for installation.

Features.

- Duct type of TOTAKU SD-AS.
- With special formulation of soft PVC, the anti-static effect will last as shown in the under-mentioned table (Refer to Table 2 in P.39).

Applications.

- For exhaust from room which dislikes static electricity, etc.
- For dust collecting of woodwork machine.
- For transportation of powder, etc.

FLUORO SERIES

ECO SERIES

Hose for foodstuffs

Duct hose

Hose for general suction and deliveries

Hose & Duct for powder and granule

Hose for pressure-resistance and abrasion resistance

Hose for abrasion resistance