







TOPJOB® S

Through/Ground Conductor/Shield and Ex Terminal Blocks 2.5 (4) mm²

2002 Series

| | | |
|---|--|--|
| 0.25 ... 2.5 (4) mm ² ① AWG 22 ... 12 800 V/8 kV/3 ② I _N 24 A (32 A) Terminal block width 5.2 mm / 0.205 in.  10 ... 12 mm / 0.43 in. ③ | 0.25 ... 2.5 (4) mm ² ① AWG 22 ... 12 800 V/8 kV/3 ② I _N 24 A (32 A) Terminal block width 5.2 mm / 0.205 in.  10 ... 12 mm / 0.43 in. ③ | 0.25 ... 2.5 (4) mm ² ① AWG 22 ... 12 800 V/8 kV/3 ② I _N 24 A (32 A) Terminal block width 5.2 mm / 0.205 in.  10 ... 12 mm / 0.43 in. ③ |
|---|--|--|



| Item No. | Pack. Unit | Item No. | Pack. Unit | Item No. | Pack. Unit |
|---|------------|---|------------|---|------------|
| 2-conductor through terminal block | | 3-conductor through terminal block | | 4-conductor through terminal block | |
| gray ⑤ 2002-1201 ⑤ 100 | | gray ⑤ 2002-1301 ⑤ 100 | | gray ⑤ 2002-1401 ⑤ 100 | |
| blue ⑤ 2002-1204 ④ ⑤ 100 | | blue ⑤ 2002-1304 ④ ⑤ 100 | | blue ⑤ 2002-1404 ④ ⑤ 100 | |
| orange ⑤ 2002-1202 ⑤ 100 | | orange ⑤ 2002-1302 ⑤ 100 | | orange ⑤ 2002-1402 ⑤ 100 | |
| red ⑤ 2002-1203 ⑤ 100 | | red ⑤ 2002-1303 ⑤ 100 | | red ⑤ 2002-1403 ⑤ 100 | |
| black ⑤ 2002-1205 ⑤ 100 | | black ⑤ 2002-1305 ⑤ 100 | | black ⑤ 2002-1405 ⑤ 100 | |
| yellow ⑤ 2002-1206 ⑤ 100 | | yellow ⑤ 2002-1306 ⑤ 100 | | yellow ⑤ 2002-1406 ⑤ 100 | |
| 2-conductor ground terminal block | | 3-conductor ground terminal block | | 4-conductor ground terminal block | |
| green-yellow ⑤ 2002-1207 ⑤ 100 | | green-yellow ⑤ 2002-1307 ⑤ 100 | | green-yellow ⑤ 2002-1407 ⑤ 100 | |
| | | 3-conductor shield terminal block | | 4-conductor shield terminal block | |
| | | white 2002-1308 100 | | white 2002-1408 100 | |
| Other terminal blocks with the same profile: | | Other terminal blocks with the same profile: | | Other terminal blocks with the same profile: | |
| Diode 2002-1211/1000-411 Page 82 | | Diode 2002-1311/1000-411 Page 82 | | Diode 2002-1411/1000-411 Page 82 | |
| | | LED 2002-1321/1000-434 Page 82 | | LED 2002-1421/1000-434 Page 82 | |
| | | | | Double-potential 2002-1441 Page 15 | |
| Item-Specific Accessories | | Item-Specific Accessories | | Item-Specific Accessories | |
| End and intermediate plate, 0.8 mm thick | | End and intermediate plate, 0.8 mm thick | | End and intermediate plate, 0.8 mm thick | |
| orange 2002-1292 100 (4x25) | | orange 2002-1392 100 (4x25) | | orange 2002-1492 100 (4x25) | |
| gray 2002-1291 100 (4x25) | | gray 2002-1391 100 (4x25) | | gray 2002-1491 100 (4x25) | |
| Separator, oversized, 2 mm thick | | Separator, oversized, 2 mm thick | | Separator, oversized, 2 mm thick | |
| orange 2002-1294 100 (4x25) | | orange 2002-1394 100 (4x25) | | orange 2002-1494 100 (4x25) | |
| gray 2002-1293 100 (4x25) | | gray 2002-1393 100 (4x25) | | gray 2002-1493 100 (4x25) | |
| Ex e/Ex i separator, orange, 3 mm thick | | Ex e/Ex i separator, orange, 3 mm thick | | Ex e/Ex i separator, orange, 3 mm thick | |
| 90 mm 209-190 50 (2x25) | | 120 mm 209-191 50 (2x25) | | 120 mm 209-191 50 (2x25) | |

2002 Series Accessories

Appropriate marking systems: WMB/Marking strips/WMB Inline (see Section 13)

| Insulation stop, | Push-in type jumper bar, insulated, | Push-in type jumper bar, insulated, |
|---|---|---|
| 5 pcs/strip, 0.25 ... 0.5 mm ² light gray 2002-171 200 (8x25) | ⑥ I _N 25 A, light gray 2-way 2002-402 200 (8x25) | I _N 25 A, light gray from 1 to 3 2002-433 200 (8x25) |
| | 3-way 2002-403 200 (8x25) | from 1 to 4 2002-434 200 (8x25) |
| | 4-way 2002-404 200 (8x25) | from 1 to 5 2002-435 100 (4x25) |
| | 5-way 2002-405 100 (4x25) | from 1 to 6 2002-436 100 (4x25) |
| | 6-way 2002-406 100 (4x25) | from 1 to 7 2002-437 100 (4x25) |
| | 7-way 2002-407 100 (4x25) | from 1 to 8 2002-438 100 (4x25) |
| | 8-way 2002-408 100 (4x25) | from 1 to 9 2002-439 100 (4x25) |
| | 9-way 2002-409 100 (4x25) | from 1 to 10 2002-440 100 (4x25) |
| | 10-way 2002-410 100 (4x25) | |
| Insulation stop, 5 pcs/strip, 0.75 ... 1 mm ² dark gray 2002-172 200 (8x25) | | |
| Protective warning marker, with high-voltage symbol, black, for 5 terminal blocks yellow 2002-115 100 (4x25) | | |