





0.08 ... 2.5 (4" f-st") mm ² ① 500 V/6 kV/3 ② I _N 16 A Terminal block width 5 mm / 0.197 in. 6 ... 7 mm / 0.26 in. ③	AWG 28 ... 12 300 V, 20 A ④	0.08 ... 2.5 (4" f-st") mm ² ① 500 V/6 kV/3 ② I _N 16 A Terminal block width 5 mm / 0.197 in. 6 ... 7 mm / 0.26 in. ③	AWG 28 ... 12
--	--------------------------------	--	---------------











- ① Max. insulation diameter: 4.4 mm
- ② 500 V = rated voltage
6 kV = rated surge voltage
3 = pollution degree
(also see Section 14)
- ③ Strip length, see packaging or instructions.
- ④ See application notes for:
Insulation stop, page 293
- ⑤ Note:
2-conductor female plug is not suitable.

Item No.	Pack. Unit	Item No.	Pack. Unit
1-conductor/1-pin double-deck carrier terminal block, through/through terminal block, gray housing		1-conductor/1-pin double-deck carrier terminal block, ground conductor/through terminal block, gray housing	
○ L/L 870-101	50	○ PE/N 870-117	50
○ N/L 870-102	50	○ PE/L 870-127	50
○ L/N 870-103	50		
1-conductor/1-pin double-deck carrier terminal block, through/through terminal block, blue housing			
● N/N 870-104	50		
Other terminal blocks with the same profile:			
Through 870-501	Page 374		



Item No.	Pack. Unit	Item No.	Pack. Unit
2-conductor/2-pin double-deck carrier terminal block, 2-conductor/2-pin through terminal block, internal commoning, conductor entry with violet marking, gray housing		2-conductor/2-pin double-deck carrier terminal block, 2-conductor/2-pin ground conductor terminal block, internal commoning, green-yellow housing	
○ L 870-108	50	● PE 870-107	50
2-conductor/2-pin double-deck carrier terminal block, 2-conductor/2-pin through terminal block, internal commoning, conductor entry with violet marking, blue housing			
● N 870-109	50		

Accessories			
Appropriate marking system: Miniature WSB/WMB (see Section 13)			
End and intermediate plate, 1 mm thick			
	orange 870-119	100	(4x25)
	gray 870-118	100	(4x25)
Insulation stop,			
④ 	5 pcs/strip, 0.08 ... 0.2 mm ² "s" (0.14 mm ² "f-st") white 280-470	200	(8x25)
Push-in type jumper bar, insulated,			
	I _N 18 A, light gray		
	2-way 870-402	200	(8x25)
	3-way 870-403	200	(8x25)
	4-way 870-404	100	(4x25)
	5-way 870-405	100	(4x25)
	6-way 870-406	100	(4x25)
	7-way 870-407	100	(4x25)
	8-way 870-408	100	(4x25)
	9-way 870-409	100	(4x25)
	10-way 870-410	50	(2x25)
Push-in type jumper bar, insulated,			
	I _N 18 A, light gray		
	from 1 to 3 870-433	200	(8x25)
	from 1 to 4 870-434	200	(8x25)
	from 1 to 5 870-435	100	(4x25)
	from 1 to 6 870-436	100	(4x25)
	from 1 to 7 870-437	100	(4x25)
	from 1 to 8 870-438	100	(4x25)
	from 1 to 9 870-439	100	(4x25)
	from 1 to 10 870-440	50	(2x25)
Coding pin,			
	for coding female plugs orange 769-435	100	(4x25)
Pin cover,			
	with receptacle for miniature WSB gray 769-438	100	(4x25)
	orange 769-439	100	(4x25)
1-conductor female plug,			
	angled gray 769-101/022-000		200
1-conductor female plug,			
⑤ 	straight gray 769-101		200