



Size  $\phi 3 \sim \phi 10$

# C-CTE4000

Super MG
UT COAT
30°
Flatland
±5'
Shank Dia 0/-0.005

Material Applications (★ Highly Recommended ● Recommended ○ Suggested)

Work Material																	
Carbon Steels S45C S55C	Alloy Steels SK / SCM SUS	Prehardened Steels NAK HPM	Hardened Steels					Cast Iron	Aluminum Alloys	Graphite	Copper	Plastics	Glass Filled Plastics	Titanium Alloys	Heat Resistant Alloys	Cemented Carbide	Hard Brittle (Non-Metallic) Materials
			~50HRC	~55HRC	~60HRC	~65HRC	~70HRC										
●	●	●	●	●							○						

## Features

Extensive line up of tapered design from 30' to 7° of half included angle. Refer to page 564 for 2 flute C-CTE.

Total 46 models

Unit (mm)

Model Number	Tip Diameter	Half Included Angle	Length of Cut	Dia. at Large End	Overall Length	Shank Diameter	Suggested Retail Price ¥
C-CTE 4030-1	3	30'	10	3.17	50	6	11,340
C-CTE 4030-2		1°		3.35	50	6	11,340
C-CTE 4030-3		1°30'		3.52	50	6	11,340
C-CTE 4030-4		2°		3.70	50	6	11,340
C-CTE 4030-5		2°30'		3.87	50	6	11,340
C-CTE 4030-6		3°		4.05	50	6	11,340
C-CTE 4030-10		5°		4.75	50	6	12,290
C-CTE 4030-14		7°		5.46	50	6	13,650
C-CTE 4040-1	4	30'	15	4.26	50	6	11,760
C-CTE 4040-2		1°		4.52	50	6	11,760
C-CTE 4040-3		1°30'		4.79	50	6	11,760
C-CTE 4040-4		2°		5.05	50	6	11,760
C-CTE 4040-5		2°30'		5.31	50	6	11,760
C-CTE 4040-6		3°		5.57	50	6	11,760
C-CTE 4040-10		5°		6.63	50	8	16,280
C-CTE 4040-14		7°		7.68	50	8	18,150

Next Page ➔

- φ3mm Shank V Series
- UDC-PCD Series
- CBN Series
- Square
- Long Neck Square
- Radius
- Long Neck Radius
- Taper Neck Radius
- Ball / Long Shank Ball
- Long Neck Ball
- Taper Neck Ball
- Taper
- Barrel
- Spiral V Cutter
- Drill
- Technical Data