




DIN-rail mount PCB carrier Size 1	DIN-rail mount PCB carrier Size 2	DIN-rail mount PCB carrier Size 2 with cover and end plates
---	---	--



L_1 = PCB length
 $L_2 = L_1 - 11$ mm (L_2 = Carrier base length)
 $L_3 = L_1 + 2$ mm




L_1 = PCB/Cover length
 $L_2 = L_1 - 15,8$ mm (L_2 = Base length)
 $L_3 = L_1 + 2$ mm



Item No.	Length	Pack. Unit	Item No.	Length	Pack. Unit	Item No.	Length	Pack. Unit
DIN-rail mount PCB carrier, size 1			DIN-rail mount PCB carrier, size 2			DIN-rail mount PCB carrier, size 2 with cover		
End plate, size 1			End plate, size 2			End plate, size 2, "high"		
288-601		1	288-621		1	288-626		1
Mounting foot for DIN 35 rail			Mounting foot for DIN 35 rail			Cover, size 2		
288-602		1	288-622		1	288-627	1 m	1
Carrier base, size 1			Carrier base, size 2					
288-600	1 m	1	288-620	1 m	1			
Phillips screw 2.9 x 13*			Phillips screw 2.9 x 13*					
210-533		25	210-533		25			
Marking strips 7.5 x 0.5 mm								
translucent	709-196	1 m						
white	709-198	1 m						
PCB is not included.			PCB is not included.			PCB is not included.		

Minimum PCB length without carrier base, size 1: $L_1 = 11$ mm, size 2: $L_1 = 15.8$ mm
 Free space between base and PCB bottom side: 5 mm
 PCB tolerances: 1.5 mm \pm 0.2 mm (thickness), \pm 0.2 mm (length/width); -0.1/+0.3 for milling contours



* 2 pcs per lateral cover. Can be used with a module length of 35 mm or higher. Side covers must be riveted for smaller modules. Rivet length depends on module length. Rivets are not part of our product line.