


FF Type Support Unit

Round Type for Support



RoHS COMPLIANT REACH The new EU chemicals legislation



Please, download CAD DATA from www.sungilfa.com

FF 6 ~ 30

4-ØX DRILL, THRU
ØY C'BORE, DP Z



Note

1. The surfaces A and B are reference for installation. Please, use the accurate size spacer if adjusting height is necessary.



Unit : mm

Model No.	d ₁	L	H	F	D	A	PCD	B	X	Y	Z	Mass (g)	Bearing	Snap Ring
FF6-8	6	10	6	4	22	36	28	28	3.4	6.5	3	30	606ZZ	C6
FF10	8	12	7	5	28	43	35	35	3.4	6.5	4	60	608ZZ	C8
FF12	10	15	7	8	34	52	42	42	4.5	8	4	100	6000ZZ	C10
FF15	15	17	9	8	40	63	50	52	5.5	9.5	5.5	140	6002ZZ	C15
FF17	17	20	11	9	50	77	62	61	6.5	11	6.5	290	6203ZZ	C17
FF20	20	20	11	9	57	85	70	68	6.6	11	6.5	380	6204ZZ	C20
FF25	25	24	14	10	63	98	80	79	9	14	8.5	590	6205ZZ	C25
FF30	30	27	18	9	75	117	95	93	11	17.5	11	930	6206ZZ	C30