

No. VE-1500



Lever type DC Type 16-step×5scales



No. VE-2000



Lever type DC Type 16-step×5scales




No. VE-3000




Lever type DC Type 16-step×8scales




No. VE-4000




Lever type DC Type High-speed revolution 16-step×8scales




No. VE-4000P



Push type DC Type High-speed revolution 16-step×8scales




No. VE-4500



Lever type DC Type 16-step×8scales



No. VE-4500P



Push type DC Type 16-step×8scales



- Slot-less/brush-less motor is used. Tightening accuracy, efficiency and maintainability are improved.
- Easy-to-use ergonomic design. Shock absorbing gel pad enables a firm grip.
- Prevents mis-operation of adjustment by a tamper-proof sleeve. ●Power cable (2m) integrated type without a connector on the main body.
- VE-1500/2000 have connectors, and only the main body can be removed. Power cable length is 2m.

Model No.	Output torque range (N·m)	Applicable screws Small screw Tapping (mm)	No-load rotation speed (min ⁻¹)	Rating	External dimensions (mm)	Weight (g)	Enclosed bits	Controller	EDP No.
VE-1500	0.01~0.15	M1.0~1.7	1.0~1.5	HI 1000/LO 700	12VDC 15W	200 190	D73 Φ 0×1.4×40...1/ Φ 0×1.7×40...1	VCT-20	550001
VE-2000	0.06~0.34	M1.0~2.3	1.0~2.0	HI 1000/LO 700	12VDC 15W	200 190	D73 Φ 0×1.4×40...1/ Φ 0×1.7×40...1	VCT-20	550002
VE-3000	0.15~1.0	M2.0~3.0	1.6~2.6	HI 1000/LO 700	32VDC 25W	222 430	D73 Φ 0×1.7×40...1/ Φ 1× 3×40...1	VCT-30	550003
VE-3000U								—	550103
VE-4000	0.3~1.5	M2.5~4.0	1.6~2.6	HI 2000/NoLO setting	32VDC 55W	250 700	B36 Φ 1×70...1/ Φ 2×70...1	VCT-45	550004
VE-4000U								—	550104
VE-4000P	0.3~1.5	M2.5~4.0	1.6~2.6	HI 2000/NoLO setting	32VDC 55W	250 700	B36 Φ 1×70...1/ Φ 2×70...1	VCT-45	550005
VE-4000PU								—	550105
VE-4500	0.4~1.8	M3.0~4.0	2.3~3.0	HI 1000/LO 700	32VDC 55W	250 710	B36 Φ 1×70...1/ Φ 2×70...1	VCT-45	550006
VE-4500U								—	550106
VE-4500P	0.4~1.8	M3.0~4.0	2.3~3.0	HI 1000/LO 700	32VDC 55W	250 710	B36 Φ 1×70...1/ Φ 2×70...1	VCT-45	550007
VE-4500PU								—	550107

*Common accessories for products with controllers: 1 tamper-proof sleeve, 2 set screws (M3×3), 1 hexagonal wrench (H1.5), 1 AC cable (1.8 m), 1 3P2P conversion adapter, user manual Material: PC+elastomer
 *Common accessories for products without controllers: 1 tamper-proof sleeve, 2 set screws (M3 × 3), 1 hexagonal wrench (H1.5), user manual Material: PC + elastomer