




TOPJOB® S

Through/Ground Conductor/Shield and Ex Terminal Blocks 1.5 (2.5) mm²

2001 Series

0.25 ... 1.5 (2.5) mm ² ① AWG 22 ... 14 800 V/8 kV/3 ② I _N 18 A (24 A) Terminal block width 4.2 mm / 0.165 in. 9 ... 11 mm / 0.39 in. ③	0.25 ... 1.5 (2.5) mm ² ① AWG 22 ... 14 800 V/8 kV/3 ② I _N 18 A (24 A) Terminal block width 4.2 mm / 0.165 in. 9 ... 11 mm / 0.39 in. ③	0.25 ... 1.5 (2.5) mm ² ① AWG 22 ... 14 800 V/8 kV/3 ② I _N 18 A (24 A) Terminal block width 4.2 mm / 0.165 in. 9 ... 11 mm / 0.39 in. ③
--	--	--



Item No.	Pack. Unit	Item No.	Pack. Unit	Item No.	Pack. Unit
2-conductor through terminal block		3-conductor through terminal block		4-conductor through terminal block	
gray ⑤ 2001-1201 ⑤ 100		gray ⑤ 2001-1301 ⑤ 100		gray ⑤ 2001-1401 ⑤ 100	
blue ⑤ 2001-1204 ④ ⑤ 100		blue ⑤ 2001-1304 ④ ⑤ 100		blue ⑤ 2001-1404 ④ ⑤ 100	
orange ⑤ 2001-1202 ⑤ 100		orange ⑤ 2001-1302 ⑤ 100		orange ⑤ 2001-1402 ⑤ 100	
red ⑤ 2001-1203 ⑤ 100		red ⑤ 2001-1303 ⑤ 100		red ⑤ 2001-1403 ⑤ 100	
black ⑤ 2001-1205 ⑤ 100		black ⑤ 2001-1305 ⑤ 100		black ⑤ 2001-1405 ⑤ 100	
yellow ⑤ 2001-1206 ⑤ 100		yellow ⑤ 2001-1306 ⑤ 100		yellow ⑤ 2001-1406 ⑤ 100	
2-conductor ground terminal block		3-conductor ground terminal block		4-conductor ground terminal block	
green-yellow ⑤ 2001-1207 ⑤ 100		green-yellow ⑤ 2001-1307 ⑤ 100		green-yellow ⑤ 2001-1407 ⑤ 100	
Other terminal blocks with the same profile:		Other terminal blocks with the same profile:		Other terminal blocks with the same profile:	
Diode 2001-1211/1000-411 Page 80		Diode 2001-1311/1000-411 Page 80		Diode 2001-1411/1000-411 Page 80	
		LED 2001-1321/1000-434 Page 80		LED 2001-1421/1000-434 Page 80	
				Double-potential 2001-1441 Page 13	
Item-Specific Accessories		Item-Specific Accessories		Item-Specific Accessories	
End and intermediate plate, 0.8 mm thick		End and intermediate plate, 0.8 mm thick		End and intermediate plate, 0.8 mm thick	
orange 2002-1292 100 (4x25)		orange 2002-1392 100 (4x25)		orange 2002-1492 100 (4x25)	
gray 2002-1291 100 (4x25)		gray 2002-1391 100 (4x25)		gray 2002-1491 100 (4x25)	
Separator, oversized, 2 mm thick		Separator, oversized, 2 mm thick		Separator, oversized, 2 mm thick	
orange 2002-1294 100 (4x25)		orange 2002-1394 100 (4x25)		orange 2002-1494 100 (4x25)	
gray 2002-1293 100 (4x25)		gray 2002-1393 100 (4x25)		gray 2002-1493 100 (4x25)	
Ex e/Ex i separator, orange, 3 mm thick		Ex e/Ex i separator, orange, 3 mm thick		Ex e/Ex i separator, orange, 3 mm thick	
90 mm 209-190 50 (2x25)		120 mm 209-191 50 (2x25)		120 mm 209-191 50 (2x25)	

2001 Series Accessories

Appropriate marking systems: WMB/WMB Inline/Marking strips
(see Section 13)

Insulation stop,	Push-in type jumper bar, insulated,	Push-in type jumper bar, insulated,
5 pcs/strip, 0.25 ... 0.5 mm ² light gray 2001-171 200 (8x25)	I _N 18 A, light gray 2-way 2001-402 200 (8x25) 3-way 2001-403 200 (8x25) 4-way 2001-404 200 (8x25) 5-way 2001-405 100 (4x25) 6-way 2001-406 100 (4x25) 7-way 2001-407 100 (4x25) 8-way 2001-408 100 (4x25) 9-way 2001-409 100 (4x25) 10-way 2001-410 100 (4x25)	I _N 18 A, light gray from 1 to 3 2001-433 200 (8x25) from 1 to 4 2001-434 200 (8x25) from 1 to 5 2001-435 100 (4x25) from 1 to 6 2001-436 100 (4x25) from 1 to 7 2001-437 100 (4x25) from 1 to 8 2001-438 100 (4x25) from 1 to 9 2001-439 100 (4x25) from 1 to 10 2001-440 100 (4x25)
Step-down jumper, insulated, I _N 32 A light gray 2006-499 50 (2x25)		
Protective warning marker, with high-voltage symbol, black, for 5 terminal blocks yellow 2001-115 100 (4x25)		