



















Modular Terminal Blocks with Fixing Flange or Snap-In Mounting Foot 1.5 mm²

260 Series

0.08 ... 1.5 mm ² 400 V/6 kV/3 ① I _N 18 A Terminal block width 5 mm / 0.197 in.  8 ... 9 mm / 0.33 in. ②	AWG 28 ... 16 300 V, 10 A ③ 300 V, 15 A ③	0.08 ... 1.5 mm ² 400 V/6 kV/3 ① I _N 18 A Terminal block width 8 mm / 0.315 in.  8 ... 9 mm / 0.33 in. ②	AWG 28 ... 16 300 V, 10 A ③ 300 V, 15 A ③
--	---	---	---



- ① 400 V = rated voltage
6 kV = rated surge voltage
3 = pollution degree
(also see Section 14)
- ② Strip length, see packaging or instructions.
- ③ See application notes for:
Test plug module, page 416

Color	Item No.	Pack. Unit	Color	Item No.	Pack. Unit	260 Series Accessories	
2-conductor terminal block with fixing flange, for screw or similar mounting types, fixing hole 3.2 mm Ø, with 209-123 mounting adapter also for DIN 35 rail			4-conductor terminal block with fixing flange, for screw or similar mounting types, fixing hole 3.2 mm Ø, with 209-123 mounting adapter also for DIN 35 rail			Marking accessories, see Section 13	
gray	260-301	300 (6x50)	gray	260-331	300 (6x50)	Aluminum carrier rail , 1000 mm long, 18 mm wide, 7 mm high  210-154 1	
light gray	260-303	300 (6x50)	light gray	260-333	300 (6x50)	End stop , for WSB Quick markers, for 210-154 aluminum rail, 6 mm wide  209-122 25	
blue	260-304	300 (6x50)	blue	260-334	300 (6x50)	Mounting foot , for DIN 35 rail, can be snapped on terminal blocks with snap-in mounting foot, 6.4 mm wide  209-120 25	
orange	260-306	300 (6x50)	orange	260-336	300 (6x50)	Mounting foot with screw , for DIN 35 rail, can be screwed on terminal blocks with fixing flange, 6.4 mm wide  209-123 25	
green-yellow	260-307	300 (6x50)	green-yellow	260-337	300 (6x50)	Mounting adapter , for DIN 35 rail, can be used as end plate, 6.5 mm wide  209-137 25	
2-conductor terminal block with snap-in mounting foot, for plate thickness 0.6 ... 1.2 mm, fixing hole 3.5 mm Ø, fits 210-154 aluminum rail or with 209-120 mounting adapter for DIN 35 rail			4-conductor terminal block with snap-in mounting foot, for plate thickness 0.6 ... 1.2 mm, fixing hole 3.5 mm Ø, fits 210-154 aluminum rail or with 209-120 mounting adapter for DIN 35 rail			Test plug , with 500 mm cable, 2 mm Ø  210-136 50	
gray	260-311	300 (6x50)	gray	260-341	300 (6x50)	Test plug , with 500 mm cable, 2.3 mm Ø  210-137 50	
light gray	260-313	300 (6x50)	light gray	260-343	300 (6x50)	Operating tool with partially insulated shaft , type 2, (3.5 x 0.5) mm blade  210-720 1	
blue	260-314	300 (6x50)	blue	260-344	300 (6x50)		
orange	260-316	300 (6x50)	orange	260-346	300 (6x50)		
green-yellow	260-317	300 (6x50)	green-yellow	260-347	300 (6x50)		
2-conductor end terminal block, without fixing foot, for terminal strips with snap-in mounting feet			4-conductor end terminal block, without fixing foot, for terminal strips with snap-in mounting feet				
gray	260-321	300 (6x50)	gray	260-351	300 (6x50)		
light gray	260-323	300 (6x50)	light gray	260-353	300 (6x50)		
blue	260-324	300 (6x50)	blue	260-354	300 (6x50)		
orange	260-326	300 (6x50)	orange	260-356	300 (6x50)		
green-yellow	260-327	300 (6x50)	green-yellow	260-357	300 (6x50)		
Item-Specific Accessories			Item-Specific Accessories				
Test plug module , can be snapped together, 5 mm wide  gray 249-135 100 (4x25)			Test plug module , can be snapped together, 8 mm wide  gray 249-138 100 (4x25)				
Test plug module with locking levers , can be snapped together, 5 mm wide  gray 260-404 100 (4x25)			Test plug module with locking levers , can be snapped together, 8 mm wide  gray 260-405 100 (4x25)				
260 Series Accessories							
For marking accessories, see Section 13							
End plate with fixing flange  gray 260-361 300 (6x50)			Comb-style jumper bar , insulated, I _N 10 A, gray, reduces maximum conductor size to 1 mm ² /AWG 16  2-way 260-402 25				
End plate with snap-in mounting foot  gray 260-371 300 (6x50)			Operating tool , of insulating material, for inserting comb-style jumper bars  2-way 209-132 1				