

Modular Terminal Blocks with Fixing Flange or Snap-In Mounting Foot 2.5 mm² 261 Series

| | | | |
|---|--|--|--|
| <p>0.08 ... 2.5 mm² 500 V/6 kV/3 ① I_N 24 A</p> <p>Terminal block width 6 mm / 0.236 in. 8 ... 9 mm / 0.33 in. ②</p> | <p>AWG 28 ... 14 300 V, 15 A ④ 300 V, 20 A ④</p> | <p>0.08 ... 2.5 mm² 500 V/6 kV/3 ① I_N 24 A</p> <p>Terminal block width 10 mm / 0.394 in. 8 ... 9 mm / 0.33 in. ②</p> | <p>AWG 28 ... 14 300 V, 15 A ④ 300 V, 20 A ④</p> |
|---|--|--|--|



- ① 500 V = rated voltage
6 kV = rated surge voltage
3 = pollution degree
(also see Section 14)
- ② Strip length, see packaging or instructions.
- ③ Suitable for Ex i applications
- ④ See application notes for:
Test plug module, page 416

| Color | Item No. | Pack. Unit | Color | Item No. | Pack. Unit | 261 Series Accessories |
|--|-----------|------------|--|-----------|------------|--|
| 2-conductor terminal block with fixing flange, for screw or similar mounting types, fixing hole 3.2 mm Ø, with 209-123 mounting adapter also for DIN 35 rail | | | 4-conductor terminal block with fixing flange, for screw or similar mounting types, fixing hole 3.2 mm Ø, with 209-123 mounting adapter also for DIN 35 rail | | | Marking accessories, see Section 13 |
| gray | 261-301 | 200 (4x50) | gray | 261-331 | 200 (4x50) | Aluminum carrier rail , 1000 mm long, 18 mm wide, 7 mm high 210-154 1 |
| light gray | 261-303 | 200 (4x50) | light gray | 261-333 | 200 (4x50) | End stop , for WSB Quick markers, for 210-154 aluminum rail, 6 mm wide 209-122 25 |
| blue | 261-304 ③ | 200 (4x50) | blue | 261-334 ③ | 200 (4x50) | |
| orange | 261-306 | 200 (4x50) | orange | 261-336 | 200 (4x50) | |
| green-yellow | 261-307 | 200 (4x50) | green-yellow | 261-337 | 200 (4x50) | |
| 2-conductor terminal block with snap-in mounting foot, for plate thickness 0.6 ... 1.2 mm, fixing hole 3.5 mm Ø, fits 210-154 aluminum rail or with 209-120 mounting adapter for DIN 35 rail | | | 4-conductor terminal block with snap-in mounting foot, for plate thickness 0.6 ... 1.2 mm, fixing hole 3.5 mm Ø, fits 210-154 aluminum rail or with 209-120 mounting adapter for DIN 35 rail | | | Mounting foot , for DIN 35 rail, can be snapped on terminal blocks with snap-in mounting foot, 6.4 mm wide gray 209-120 25 |
| gray | 261-311 | 200 (4x50) | gray | 261-341 | 200 (4x50) | Mounting foot with screw , for DIN 35 rail, can be screwed on terminal blocks with fixing flange, 6.4 mm wide gray 209-123 25 |
| light gray | 261-313 | 200 (4x50) | light gray | 261-343 | 200 (4x50) | |
| blue | 261-314 ③ | 200 (4x50) | blue | 261-344 ③ | 200 (4x50) | |
| orange | 261-316 | 200 (4x50) | orange | 261-346 | 200 (4x50) | |
| green-yellow | 261-317 | 200 (4x50) | green-yellow | 261-347 | 200 (4x50) | Mounting adapter , for DIN 35 rail, can be used as end plate, 6.5 mm wide gray 209-137 25 |
| 2-conductor end terminal block, without fixing foot, for terminal strips with snap-in mounting feet | | | 4-conductor end terminal block, without fixing foot, for terminal strips with snap-in mounting feet | | | Test plug , with 500 mm cable, 2 mm Ø red 210-136 50 |
| gray | 261-321 | 200 (4x50) | gray | 261-351 | 200 (4x50) | Test plug , with 500 mm cable, 2.3 mm Ø yellow 210-137 50 |
| light gray | 261-323 | 200 (4x50) | light gray | 261-353 | 200 (4x50) | |
| blue | 261-324 ③ | 200 (4x50) | blue | 261-354 ③ | 200 (4x50) | |
| orange | 261-326 | 200 (4x50) | orange | 261-356 | 200 (4x50) | |
| green-yellow | 261-327 | 200 (4x50) | green-yellow | 261-357 | 200 (4x50) | Operating tool with partially insulated shaft , type 2, (3.5 x 0.5) mm blade 210-720 1 |
| Item-Specific Accessories | | | Item-Specific Accessories | | | |
| Test plug module , can be snapped together, 6 mm wide gray 249-136 100 (4x25) | | | Test plug module , can be snapped together, 10 mm wide gray 249-139 100 (4x25) | | | |
| Test plug module with locking levers , can be snapped together, 6 mm wide gray 261-404 100 (4x25) | | | Test plug module with locking levers , can be snapped together, 10 mm wide gray 261-405 100 (4x25) | | | |
| 261 Series Accessories | | | | | | |
| For marking accessories, see Section 13 | | | | | | |
| End plate with fixing flange gray 261-361 300 (6x50) | | | Comb-style jumper bar , insulated, I _N 16 A, gray, reduces maximum conductor size to 1.5 mm ² /AWG 16 2-way 261-402 25 | | | |
| End plate with snap-in mounting foot gray 261-371 300 (6x50) | | | Operating tool , of insulating material, for inserting comb-style jumper bars 2-way 209-132 1 | | | |