

**Stripping tools with automatic self-adjustment**

- For flexible and solid conductors
- Ideally suitable for mechanical and plant engineering, railway and rail traffic, wind energy, robot technology, explosion protection as well as marine, offshore and ship building sectors
- Stripping length adjustable via end stop
- Automatic opening of clamping jaws after stripping
- No fanning-out of individual conductors
- Adjustable to diverse insulation thicknesses
- Double-insulated cables in two process steps without special adjustment
- No play in self-adjusting cutting unit
- Long service life
- Optimised ergonomic design
- Selectable two-stage partial stripping



**Technical data**

Max. stripping performance	
Cable type	
Wire cross-section, min. / max.	
Stripping length, max.	mm
Cutting performance	
Conductor cross-section (cutting capacity)	mm <sup>2</sup>
Tool data	
Length	mm
Weight	g
Note	

**Ordering data**

Version
Note

**Accessories**

Type	Qty.	Order No.
ERME SPX UL	1	1471390000
Note		

**stripax® Ultimate**

0.25...6 mm<sup>2</sup>



- Stripping and cutting of flexible and solid conductors from 0.25...6 mm<sup>2</sup> (~AWG 24... 10)
- Especially suitable for UL-specified conductors and halogen-free insulation materials



**STRIPAX ULTIMATE**

Flexible and solid conductors with halogen-free insulation		
Wire cross-section, min. / max.	0.25...6	
Stripping length, max.	25	
Cutting performance		
Conductor cross-section (cutting capacity)	6	
Tool data		
Length	190	
Weight	175	
Note		

Type	Qty.	Order No.
STRIPAX ULTIMATE	1	1468880000
Note		

Type	Qty.	Order No.
ERME SPX UL	1	1471390000
Note		

**stripax® Ultimate XL**

2.5-10 mm<sup>2</sup>



- Stripping and cutting of flexible and solid conductors from 2,5 ... 10 mm<sup>2</sup> (~AWG 14 - 8)
- Especially suitable for UL-specified conductors and halogen-free insulation materials



**STRIPAX ULTIMATE XL**

Flexible and solid conductors with halogen-free insulation		
Wire cross-section, min. / max.	2.5...10	
Stripping length, max.	25	
Cutting performance		
Conductor cross-section (cutting capacity)	6	
Tool data		
Length	190	
Weight	175	
Note		

Type	Qty.	Order No.
STRIPAX ULTIMATE XL	1	1512780000
Note		

Type	Qty.	Order No.
ERME SPX UL XL	1	1512790000
Note		