

# Wheels



**WF**  
Rubber wheel with steel plate wheel assembly (including B)



**UWF**  
Urethane wheel with steel plate wheel assembly (including B)

## Wheels used in SKY SERIES $\phi$ 200

Product number	Wheels	Wheel diameter (mm)	Boss width (mm)	Wheel width (mm)	Hole diameter (mm)	Allowance load daN(kgf)
<b>WF-</b> -200	Rubber wheel with steel plate wheel assembly (including B)	200	56	43	20	250(255.0)
<b>UWF-</b> -200	Urethane wheel with steel plate wheel assembly (including B)	200	56	43	20	400(408.0)

\* Allowable load indicates allowable load only for wheels.



**SUE**  
Urethane (including B) wheel with antistatic nylon wheel

## Wheels used in SKY SERIES $\phi$ 100 and $\phi$ 125

Product number	Wheels	Wheel diameter (mm)	Boss width (mm)	Wheel width (mm)	Hole diameter (mm)	Allowance load daN(kgf)
S- 100	Urethane (equipped with bearing) wheel with antistatic nylon wheel	100	32	28	8.2	60(61.2)
125		125	37.4	32	8.2	60(61.2)

\* Allowable load indicates allowable load only for wheels.



**BN**  
Nylon wheel



Reinforced nylon wheel (including B)



MC nylon wheel (including B)  
\*Following table NB- 50 60 AF- 75 100 MC



**PB**  
Phenol wheel (including B)



**GNB**  
Reinforced nylon wheel



**MC**  
MC nylon wheel (including B)



**MCE**  
MC nylon wheel (including B) (conductive)

## Wheels used in Casters with adjuster foot

Product number	Wheels	Wheel diameter (mm)	Boss width (mm)	Wheel width (mm)	Hole diameter (mm)	Allowance load daN(kgf)
S-	BN	50	30	28	8	60(61.2)
		65	30	25	8	70(71.4)
		75	30	25	8	80(81.6)
L-	BN(B24)	40	24	21	6	40(40.8)
	BN	50	24	21	6	40(40.8)
NB-	Reinforced nylon wheel (including B)	50	56	45	12	260(265.2)
		65	56	45	12	250(255.0)
AF-	MC	75	56	45	12	300(306.0)
		100	56	45	12	300(306.0)
H-	PB	65	42	38	12.2	300(306.0)
		75	42	38	12.2	320(326.4)
H-	GNB	65	43	38	12	300(306.0)
		75	43	38	12	320(326.4)
H-	MC	65	43	38	12	300(306.0)
		75	43	38	12	320(326.4)
H-	MCE	65	43	38	12	300(306.0)
		75	43	38	12	320(326.4)

\* Allowable load indicates allowable load only for wheels.\* S-\*BN indicates wheels used in SPLG TYPE, L-\*BN indicates heels used in E-AF TYPE, NB-\* and AF-\*MC indicate wheels used in AF TYPE.

\* (including B) indicates wheels equipped with bearing.