

Shaft Collar Clamp


3-Hole / 3-Tapped (Coarse)



Type		Material	Surface Treatment	Accessory <small>Hex Socket Head Cap Screw 1 pc.</small>
3-Hole	3-Tapped			
SCST	SCSTR	S45C Equivalent	Black Oxide Coating	MSCM435 Equivalent
PSCST	PSCSTR	SUS304 Equivalent	Electroless Nickel Plating	MSUS304 Equivalent
SSCST	SSCSTR	SUS304 Equivalent	-	MSUS304 Equivalent

25 / (6.3 /)

*D6 -D25: C0.5
D30 -D50: C1



Part Number Type	B Selection D	D1	M (Coarse)	d	R	W	X	Y	P	S	3-Hole Unit Price			3-Tapped Type Unit Price			
											SCST	PSCST	SSCST	(Coarse) M1	SCSTR	PSCSTR	SSCSTR
(3-Hole) SCST PSCST SSCST	6	20	* 8	M3	3.4	1	6	4	12	3.5				M3			
			*10	M4	4.5				3.75								
	8	25	* 8	M3	3.4	1.5	8	5	14	4.5				M4			
			*10	M4	4.5				3.75								
			15	M6	6.6				6								
	10	30	* 8	M3	3.4	1.5	9	5	20	5.5				M5			
			*10	M4	4.5				3.75								
			12	M5	5.5				4.5								
	12	35	8	M3	3.4	1.5	10	5	22	5.5				M5			
			*10	M4	4.5				3.75								
			*12	M5	5.5				4.5								
	13	35	*10	M4	4.5	1.5	10	5	22	4.5				M4			
			12	M5	5.5				4.5								
			15	M6	6.6				6								
	15	40	*10	M4	4.5	1.5	11	6	23	4.5				M4			
			*12	M5	5.5				4.5								
			*15	M6	6.6				6								
	16	40	10	M5	5.5	1.5	12	6	24	4.5				M5			
			*12	M6	6.6				6								
			*15	M6	6.6				6								
20	45	*10	M5	5.5	1.5	14	7	28	5.5				M4				
		*12	M5	5.5				4.5									
		*15	M6	6.6				6									
25	50	*12	M5	5.5	1.5	15	8	34	6.6				M5				
		*15	M6	6.6				6									
		*18	M8	9				7									
30	55	*15	M6	6.6	1.5	17	10	38	6.6				M6				
		*18	M8	9				7									
		*22	M10	11				9									
35	60	*15	M6	6.6	1.5	20	10	44	6.6				M8				
		*18	M8	9				7									
		*22	M10	11				9									
40	65	*18	M8	9	2	23	12	48	9				M8				
		*22	M10	11				9									
		*25	M12	13				10									
50	75	*22	M12	13	2	26	13	56	9				M8				
		*25	M12	13				10									
		*28	M14	15				11									
60	85	*25	M12	13	3	32	16	68	11				M8				
		*28	M14	15				11									
		*32	M16	17				12									

- Due to no slitting on the opposite side of the screw, 3-Hole/3-Tapped type has less gripping power compared to 2-Hole/2-Tapped Type.
- Use of MISUMI Shafts (standard g6 and h5) is recommended.
- 2-Hole and 2-Tapped Type or Wedge Type (P285) are recommended where more shaft gripping power is required.

Ordering Example **Part Number** - **B**
SCST10 - 10