

Slit Couplings

Extra Super Duralumin - Clamping, Set Screw, Short For Servo Motors


■ **Features:** Due to the use of extra super Duralumin, it has high torsional rigidity and is applicable with servo motors.

🔗 For more misalignment tolerances and higher torque capacities, see Disc Type P.1075.


■ **For Servo Motors**



CPCX (Clamping)



CPSX (Set Screw)



*d1, d2 Identical Diameter = d1+0.5
d1, d2 Different Diameters = Large Shaft Diameter + 0.5

🔗 The lateral, angular, and axial misalignment values shown are for each occurring individually. When multiple misalignments are occurring simultaneously, the allowable maximum value of each will be reduced to 1/2.

🔗 For the selection criteria and alignment procedures, see P.1061.

Type	M	Material	S	Surface Treatment	A	Accessory
CPCX		Extra Super Duralumin		Clear Anodize		Hex Socket Head Cap Screw
CPSX						Set Screw

Part Number Type	D	d1		d2						L	ℓ	F	M1	M2	G	Unit Price							
																CPCX	CPSX						
Clamping CPCX	16	5	5	6						17.4	6	3	M3	M2	4.74								
		6		6																			
	19	5	5	6	7	8				20	6.8	3.4	M3	M2.5	5.6								
		6		6	6.35	7	8																
		6.35		6.35		8																	
		8				8	*10																
		*10					*10																
	24	6		6		8	10			25	8.5	4.25	M4	M3	8								
		6.35		6.35		8	10																
		7				8																	
		8				8	9.525	10															
		9.525					10																
10					10	*11	*12																
*11							*12																
*12							*12																
29	8			8	10	11	12		30	10.2	5.1	M4	M3	9									
	10			10	11	12	*14																
	11					12	*14																
	12						12	*14															
34	10						14		35	12	6	M5	M3	11									
	11						14																
	12						12	14							16								
	14							14							15	16							
	15														15	16							
	16															16							

🔗 CPCX is not available for * marked sizes.

Part Number Type	D	Allowable Torque (N·m)	Angular Misalignment (°)	Lateral Misalignment (mm)	Static Torsional Spring Constant (N·m/rad)	Max. Rotational Speed (r/min)	Moment of Inertia (kg·m ²)	Allowable Axial Misalignment (mm)	Screw Tightening Torque (N·m)	Correction Factor (coeff.)	Mass (g)
CPCX	16	0.5	0.5	0.05	200	39000	2.5x10 ⁻⁷	±0.1	0.5	1	7
	19	1			270	33000	5.8x10 ⁻⁷		1		12
	24	1.5			790	26000	1.8x10 ⁻⁶		23		
	29	2			1400	21000	4.7x10 ⁻⁶		41		
	34	3			2200	18000	1.1x10 ⁻⁵		62		
CPSX	16	0.5	0.5	0.05	200	39000	2.8x10 ⁻⁷	±0.1	0.7	1	7
	19	1			270	33000	6.2x10 ⁻⁷		10		
	24	1.5			790	26000	2.0x10 ⁻⁶		22		
	29	2			1400	21000	5.2x10 ⁻⁶		40		
	34	3			2200	18000	1.1x10 ⁻⁵		64		



Ordering Example

Part Number - Shaft Bore Dia. d1 - Shaft Bore Dia. d2
CPSX19 - 5 - 6