


Trims


Trims are available in 1m increment. Please note that ordering 5 pieces of L=100 means 5 rolls of 100 meter type.



Color - Pattern Samples

TR_T (Black - Extra Fine) **B-5**
 (White - Extra Fine) **W-5**
 (Gray - Wave) **G-6**
 (Black - Wave) **B-6**

TRAT
TRBT
TRCT
TRDT




Material Properties


Item	TPE	Silicon Rubber
Specific Gravity	0.95	1.2
Heat Resistance	+135°C	+200°C
Low Temp. Resistance	-60°C	-60°C
Compression Set	15~25%	16%

⚠️ TPE does not produce dioxin when burned.

Applicable Plate Thickness



Bending Directions



Features
Because of the internal metal strip, it does not require adhesives to install.

Type	Material	
	Main Body	Internal Metal Strip
TR□T	Thermoplastic Elastomer (TPE)	Aluminum
TRCS	Silicon Rubber	SPCC

Part Number Type	T	Color - Pattern	L	A	B	W	t	Minimum Bending Radius mm			Applicable Plate Thickness (T Range)
								Bending Directions①	Bending Directions②	Bending Directions③	
TRAT	0.4	B-5	L1~L100 (1m Increment)	4.4	9.7	0.4	1.9	30	30	20	0.3~0.8
	0.8			4.8	9.5	0.8					0.7~1.2
	1.6			5.6	9.1	1.6					1.2~1.6
	2.4			6.4	8.9	2.4					2.0~2.4
TRBT	0.8	B-5 W-5		5.6	11.3	0.8	2.3	40	40	20	0.6~1.2
	1.6			6.4	11.1	1.6					1.2~2.0
	2.4			7.2	11.0	2.4					2.0~3.0
	3.2			8.0	10.6	3.2					2.6~3.2
TRCT	1.6	B-5 W-5		6.0	14.5	1.6	2.2	30	30	30	1.2~2.4
	3.2			7.6	14.0	3.2					2.4~4.0
	4.8			9.2	13.3	4.8					4.0~5.0
	6.4			10.8	12.7	6.4					5.5~6.4
TRDT	3.2	B-5 W-5		7.8	19.0	3.2	2.3	50	50	50	2.3~4.0
	6.4			11.0	17.5	6.4					6.0~7.0
	8.0			12.6	16.7	8.0					7.0~8.5
	9.5			14.1	15.9	9.5					9.0~9.5
TRCS	3.2	G-6 B-6	L1~L75 (1m Increment)	17.3	14.6	12.7	2.5	50	50	50	12.0~12.7
			L1~L75 (1m Increment)	9.6	13.2	4.6					50

⚠️ Minimum bending radius value is experimental ones and not guaranteed. Use them as reference.

Ordering Example

Part Number - Color - Pattern - L

TRCT3.2 - B-5 - L6

Part Number Type	T	Color - Pattern	L	Unit Price/m						
				1~4m	5~9m	10~14m	15~29m	30~74m	75~99m	100m
TRAT	0.4	B-5	L1~L100 (1m Increment)							
	0.8									
	1.6									
	2.4									
TRBT	0.8	B-5 W-5								
	1.6									
	2.4									
	3.2									
TRCT	1.6	B-5 W-5								
	3.2									
	4.8									
	6.4									
TRDT	3.2	B-5 W-5								
	6.4									
	8.0									
	9.5									
TRCS	3.2	G-6 B-6	L1~L75 (1m Increment)							
			L1~L75 (1m Increment)							

⚠️ Specify L dimension in 1m increment.