


Bushings for Inspection Components

Straight (Standard, Press Fit Type)


For compatible Pins, see P.1819-P.1820 and P.1840.

Standard Type



RoHS 10

Material	Hardness	Surface Treatment	Type			
			P, L Selectable		P, L Configurable	
			P ^{+0.03} _{-0.01}	PH7	P ^{+0.03} _{-0.01}	PH7
SKS93 Equivalent (Raw Material)	-	-	-	-	KJBNS	KJBNSN
SKS93 Equivalent	50~60HRC	-	KJBA	KJBHA	KJBS	KJBHS
SKS93 Equivalent	50~60HRC	Electroless Nickel Plating	-	-	KJBMS	KJBHSM
SUS304 ^②	-	-	-	-	KJBSS	KJBHSS
SUS440C or 13Cr stainless	45~50HRC	-	-	-	KJBSSC	KJBHSSC



P	H7
2.00-3.00	+0.001 0
3.01-6.00	+0.012 0
6.01-10.00	+0.015 0
10.01-18.00	+0.018 0
18.01-30.00	+0.021 0
30.01-32.00	+0.025 0

①. When wall is 2mm or less ((D-P)/2≤2), R is 0.5.

P, L Selectable

Part Number Type	D	P Selection	L Selection	R	Unit Price
(P ^{+0.03}) KJBA	10	3	10	1.0	
		4	10 15	1.0	
		5	10 15	1.0	
		6	10 15	0.5	
		8	15	0.5	
	12	6	15	2.0	
		8	15 20	0.5	
		10	15	0.5	
	16	10	15 20	2.0	
		12	15 20	0.5	

Part Number Type	D	P Selection	L Selection	R	Unit Price
(PH7) KJBHA	10	4	10 15	1.0	
		5	15	1.0	
		6	15	0.5	
	12	6	15	2.0	
		8	15 20	0.5	
	16	8	20	2.0	
		10	15 20	2.0	
		13	20 25	0.5	

P, L Configurable P Dimension Tolerance^{+0.03}_{-0.01}

Part Number Type	D	P 0.01mm Increment	L 1mm Increment	R	Unit Price				
					KJBNS	KJBS	KJBMS	KJBSS	KJBSSC
(SKS93 Equivalent Raw Material) KJBNS	8	2.00~ 6.00	5~40 When P<5 L≤Px4 When P≥5 L≤Px3	1.0					
(SKS93 Equivalent Hardened) KJBS	10	2.00~ 8.00		1.0					
	12	4.00~10.00		2.0					
(SKS93 Equivalent Hardened, Electroless Nickel Plating) KJBMS	16	8.00~14.00		2.0					
	20	10.00~18.00		2.0					
(SUS304) KJBSS	25	15.00~23.00		2.0					
(SUS440C or 13Cr stainless) KJBSSC	30	20.00~27.00		2.0			-	-	-
	35	25.00~32.00		2.0			-	-	-

P, L Configurable P Dimension Tolerance H7

Part Number Type	D	P 0.01mm Increment	L 1mm Increment	R	Unit Price				
					KJBNSN	KJBHS	KJBHSM	KJBHSS	KJBHSSC
(SKS93 Equivalent Raw Material) KJBNSN	8	2.00~ 6.00	5~40 When P<5 L≤Px4 When P≥5 L≤Px3	1.0					
(SKS93 Equivalent Hardened) KJBHS	10	2.00~ 8.00		1.0					
	12	4.00~10.00		2.0					
(SKS93 Equivalent Hardened, Electroless Nickel Plating) KJBHSM	16	8.00~14.00		2.0					
	20	10.00~18.00		2.0					
(SUS304) KJBHSS	25	15.00~23.00		2.0					
(SUS440C or 13Cr stainless) KJBHSSC	30	20.00~27.00		2.0			-	-	-
	35	25.00~32.00		2.0			-	-	-

②. For SUS304, there must be a 2mm or greater wall thickness ((D-P)/2≥2). ③. D=30 and 35 are applicable to SKS93 (except electroless nickel plating) only.