



Dowel Pins

Oversized

■ Straight





Type	Material	Hardness
MS	SUJ2	58HRC~
MSC	SUS440C	58HRC~
MSCSS	SUS304	-

⚠ L1 dimension may become larger than the value shown in the catalog due to polishing process.

ℓ1	Part Number		L	Unit Price	Volume Discount Rate
	Type	D		1~499	500~2000
0.4	MS	1	6 8 10		
0.6		1.5	6 8 10		
1		2	6 8 10 15 20		
		2.5	6 8 10 15 20 25 30		
		3	6 8 10 15 20 25 30 35 40		
1.5		4	8 10 15 20 25 30 35 40 45 50		
		5	8 10 15 20 25 30 35 40 45 50		
2		6	8 10 15 20 25 30 35 40 45 50 55 60		
2.5		8	10 15 20 25 30 35 40 45 50 55 60 65 70 80		
3		10	15 20 25 30 35 40 45 50 55 60 65 70 80		
3.5		12	20 25 30 35 40 45 50 55 60 70 80		
		13	30 40 50 60 70 80		

⚠ For orders of 1 ~ 9 pc(s): Unit Price + Low Quantity Surcharge (1 Line Item)

⚠ For orders larger than indicated quantity, please check with WOS.

ℓ1	Part Number		L	Unit Price	Volume Discount Rate		
	Type	D		1 ~ 9 pc(s).	10~49	50~99	100~2000
0.4	MSC	1	5 6 8 10				
0.6		1.5	5 6 8 10				
1		2	5 6 8 10 12 15 20				
		2.5	6 8 10 12 15 20				
		3	6 8 10 12 15 20 25 30 35 40				
1.5		4	8 10 12 15 20 25 30 35 40 50				
		5	8 10 12 15 20 25 30 35 40 50				
2		6	8 10 12 15 20 25 30 35 40 50 60				
2.5		8	10 15 20 25 30 35 40 50 60				
3		10	10 15 20 25 30 35 40 50 60				
3.5		12	30 35 40 50 60				

⚠ For orders larger than indicated quantity, please check with WOS.

ℓ1	Part Number		L	Unit Price	Volume Discount Rate		
	Type	D		1 ~ 9 pc(s).	10~49	50~99	100~500
0.4	MSCSS	1	5 6 8 10				
0.6		1.5	5 6 8 10				
1		2	5 6 8 10 12 15				
		2.5	6 8 10 12 15				
		3	6 8 10 12 15 20				
1.5		4	8 10 12 15 20				
	5	10 12 15 20					
2	6	10 12 15 20 25					

⚠ For orders larger than indicated quantity, please check with WOS.