

Low Dust Generation Magnetic Catches / Low Dust Generation Thin Magnetic Catches / Plastic Catches

Low Dust Generation Magnetic Catches

RoHS 10

MGCC

Attraction Side

No.	Part Name	Material
①	Main Body	Polyacetal
②	Catch Plate	SUS430
③	Magnet	Neodymium Magnet

Part Number Type	No.	Retention Force (kgf)	Mass (g)	Color	Unit Price 1 - 9 pc (s).	Volume Discount Rate 10-50
MGCC	1	1.0	21	①Black		
	2	1.4	22	②Gray		
	3	2.0	24	③Milky White		
	4	3.3	25	④White		

- Features**
- The magnet encapsulated structure is effective for preventing rust and dust intrusions.
 - These magnetic catches are the best suited for use in clean rooms.

☞ Catch Plate is not included for No. 4.

Ordering Example Part Number
MGCC3

Low Dust Generation Thin Magnetic Catches

MGCCU

Main Body Catch Plate

Attracted State

Part Name	Material
Main Body	Polyacetal
Catch Plate	SUS430
Magnet	Neodymium Magnet

☞ Catch plate is also plastic coated.

Part Number Type	No.	Retention Force (kgf)	Mass (g)	Unit Price 1 - 9 pc (s).	Volume Discount Rate 10-100
MGCCU	1	1	14		

- Features**
- Catch plate is also plastic coated to reduce particle generation further.

Ordering Example Part Number
MGCCU1

Plastic Catches

RoHS 10

JMCG

Door

Part Name	Material
Female Side	Polyacetal
Male Side	Polyamide

ex Example

Part Number Type	No.	Retention Force (kgf)	Latching Force (kgf)	A	B	E	G	H	L	d1	d2	Mass (g)	Color	Unit Price 1-50 pcs.
JMCG	1W	1.7	2.2	26	18	6	24.5	17	2.5	3.3x6	3.3	2	Milky White	
	2B	2.7	3.1	24	17	7	22	15.5	2	2.5x5.5	2.5	1.5	Black	
	2W	2.7	3.1	24	17	7	22	15.5	2	2.5x5.5	2.5	1.5	Milky White	

Ordering Example Part Number
JMCG1W