

# Metal Joint

RoHS10



Type	Material	Plate Thickness	Surface Treatment
PBLSN	SAPH	2.6mm	Nickel Plating
PBLSNC	SUS304		

PBLSN1  
PBLSNC1  
PBLSNS1













PBLSN2  
PBLSNC2  
PBLSNS2

PBLSN3  
PBLSNC3

PBLSN4  
PBLSNC4

PBLSN5  
PBLSNC5

PBLSN6



Part Number Type	No.	Mass (g)	Components (except Bracket)			Unit Price	
			Screw	Quantity	Nut	Quantity	PBLSN, PBLSNC
PBLSN (Cathodic Electrodeposition Coating)	1	160	M6-25		M6	1	
	2	250				2	
PBLSNC (Nickel Plating)	3	325				3	
PBLSNS (Stainless Steel)	4	250				2	
	5	400				4	
PBLSN (Cathodic Electrodeposition Coating)	6	150				1	

RoHS10



Type	Material	Plate Thickness	Surface Treatment
PBLS	SAPH	2.6mm	Cathodic Electrodeposition Coating
PBLSN			

PBLSN7













PBLSN8

PBLSN9

PBLSN10

PBLSN11

PBLSN701




⚠ No nut. The main body is tapped.

⚠ A nut is welded to the main body.

Part Number Type	No.	Mass (g)	Components (except Bracket)				Unit Price	
			Screw	Quantity	Nut	Quantity	Others	PBLSN, PBL
PBLSN (Cathodic Electrodeposition Coating)	7	260	M6-25	2	M6	2		
	701	80	M6-10	1		0		
	8	200				0	Included Collar	
PBLS (Cathodic Electrodeposition Coating)	9	289	M6-25	1				
	10	186					1	Included Collar
PBLSN	11	165						

⚠ Use of PBLSN8 and PBLSN10: insert the frame through the included collar, slide the frame and the metal joint, then rotate it.

Fig. 1 Included Collar Size



Ⓜ Material: Polyethylene (White)

\* No nuts included for PBLSN8 and PBLSN9 since there is a tap on the metal bracket.

Ordering Example  
Part Number  
PBLSN1