


Stainless Steel Pipe Fittings

For tightening procedure and structure of fittings, and applicable pipe specification, refer to P.1300.

Stainless Steel Pipe Fittings Union **SKUSK**




RoHS 10 Includes ferrules (see SKFPK) Material: SUS316

Part Number Type	D	L	E	F	l	Square		Unit Price 1 - 9 pc(s).	Volume Discount Rate 10 - 30 pcs.
						Main Body h	Nut H		
SKUSK	3.18 (1/8)	37.8	2.5	13.4	24	12	12		
	4	42.6	3.5	15.3	28	14	14		
	6	42.8	5	15.4	28	14	14		
	6.35 (1/4)	42.8	5	15.4	28	14	14		
	8	44.6	6	16.8	29	14	15.87		
	9.53 (3/8)	46.6	8	17.8	31	17	19		
	10	46.6	8	17.8	31	17	19		
	12	52.6	10	22.8	31	22	23		
12.7 (1/2)	52.6	10	22.8	31	22	23			

L and F are dimensions for hand tightening.
Values in () for D dimension are by inch.

Stainless Steel Pipe Fittings Union Elbow Connectors **SKUEK**




RoHS 10 Includes ferrules (see SKFPK) Material: SUS316

Part Number Type	D	L	E	F	l	Square		Unit Price 1 - 9 pc(s).	Volume Discount Rate 10 - 30 pcs.
						Main Body h	Nut H		
SKUEK	3.18 (1/8)	24.9	2.5	13.4	18	12	12		
	4	27.8	3.5	15.3	20.5	14	14		
	6	27.9	5	15.4	20.5	14	14		
	6.35 (1/4)	27.9	5	15.4	20.5	14	14		
	8	28.8	6	16.8	21	14	15.87		
	9.53 (3/8)	30.8	8	17.8	23	17	19		
	10	30.8	8	17.8	23	17	19		
	12	34.8	10	22.8	24	22	23		
12.7 (1/2)	34.8	10	22.8	24	22	23			

L and F are dimensions for hand tightening.
Values in () for D dimension are by inch.

Stainless Steel Pipe Fittings Reducing Union **SKUSDK**




RoHS 10 Includes ferrules (see SKFPK) Material: SUS316

Part Number Type	D	D1	L	E	F1	F	l	Square		Unit Price 1 - 9 pc(s).	Volume Discount Rate 10 - 30 pcs.
								Main Body h	Nut H		
SKUSDK	6.35 (1/4)	3.18 (1/8)	40.8	2.5	15.4	13.4	26.5	14	14	12	
			4	42.7	3.5	15.4	15.3	28	14	14	14
	8	4	43.6	3.5	16.8	15.3	28.5	14	15.87	14	
			6	43.7	5	16.8	15.4	28.5	14	15.87	14
	9.53 (3/8)	6.35 (1/4)	44.7	5	17.8	15.4	29.5	17	19	14	
			6	44.7	5	17.8	15.4	29.5	17	19	14
	10	8	45.6	6	17.8	16.8	30	17	19	15.87	
			6	47.7	5	22.8	15.4	29.5	22	23	14
12	10	49.6	8	22.8	17.8	31	22	23	19		
		47.7	5	22.8	15.4	29.5	22	23	14		

L and F are dimensions for hand tightening.
Values in () for D and D1 dimension are by inch.

Stainless Steel Pipe Fittings Union Tees **SKUTK**




RoHS 10 Includes ferrules (see SKFPK) Material: SUS316

Part Number Type	D	L	E	F	l	Square		Unit Price 1 - 9 pc(s).	Volume Discount Rate 10 - 30 pcs.
						Main Body h	Nut H		
SKUTK	3.18 (1/8)	24.9	2.5	13.4	18	12	12		
	4	27.8	3.5	15.3	20.5	14	14		
	6	27.9	5	15.4	20.5	14	14		
	6.35 (1/4)	27.9	5	15.4	20.5	14	14		
	8	29.4	6	16.8	22	14	15.87		
	9.53 (3/8)	30.8	8	17.8	23	17	19		
	10	30.8	8	17.8	23	17	19		
	12	38.3	10	22.8	27.5	22	23		
12.7 (1/2)	38.3	10	22.8	27.5	22	23			

L and F are dimensions for hand tightening.
Values in () for D dimension are by inch.

Stainless Steel Pipe Fittings Port Connector **SKPCK**




RoHS 10 Material: SUS316

Part Number Type	D	L	E	l1	Unit Price 1 - 9 pc(s).	Volume Discount Rate 10 - 30 pcs.
4	26	2.5	19			
6	27	4	20			
6.35 (1/4)	27	4.8	20			
8	28	6.4	21			
9.53 (3/8)	29	7.6	22			
10	29	8	22			
12	37	9.5	26.7			
12.7 (1/2)	37	9.9	26.7			

Values in () for D dimension are by inch.

Stainless Steel Pipe Fittings Tube Insert **SKITK**



RoHS 10 Material: SUS316

Part Number Type	Tube O.D. (mm)	D	A	d	L	Unit Price 1 - 9 pc(s).	Volume Discount Rate 10 - 30 pcs.
6	5.6	4	3.0	18			
8	7	6	4.8	19			
10	9	8	6.5	20			
12	11	10	8	25			

Insert SKITK into tubes for piping Fluororesin Tubes with Stainless Steel Pipe Fittings.

Ordering Example Part Number - D1
SKUSK6 - 6.35
SKUSDK12.7 - 6.35