

Angle Brackets

Press-Fit / Standard / Ribbed

Press-Fit

STYU


Material: SS400
Surface Treatment: Trivalent Chromate (Silver)

RoHS 10

Part Number	Applicable Type	Applicable Leveling Mount No.	F	B	H	L	W	T	D		R	Unit Price
									Hole Dia.	Applicable Screw		
STYU 12	FJFN12 (P.1110)		70	13	26	130	50	9	14	M12	6.5	
16	FJFN16 (P.1110)			17	28						8.5	
20	FJFN20 (P.1110)			21	31						10.5	

Ordering Example
Part Number: **STYU12**

EX Example



Standard

Single
STYS
STTS

Double
STYD
STTD

Ribbed (Weld)
SYDR
STDR

Type	No Rib	Ribbed	Type	Material	Surface Treatment
STYS			Single	SS400	Black Oxide (Black)
STTS					Trivalent Chromate (Silver)
STYD			Double	SS400	Black Oxide (Black)
STTD					Trivalent Chromate (Silver)
SYDR			Double	SS400	Black Oxide (Black)
STDR					Trivalent Chromate (Silver)

RoHS 10

Main Body	Part Number Type	No.	H	L	T	W	D		B	A	F	G		R	P	Unit Price		
							Hole Dia.	Applicable Screw				Slotted Hole	Applicable Screw			STYS, STYD	STTS, STTD	SYDR, STDR
Single	Black Oxide STYS	10	100	75	7	45	12	M10	60	60	50	12	M10	6	-	-	-	-
	Trivalent Chromate STTS	12	150	100	9	50	16	M12	70	100	60	14	M12	7	-	-	-	-
	Black Oxide STYD (No Rib) SYDR (Ribbed)	10	100	75	7	70	12	M10	50	60	50	10	M8	5	45	-	-	-
Double	Trivalent Chromate STTD (No Rib) STDR (Ribbed)	12	150	100	9	75	16	M12	70	100	60	12	M10	6	50	-	-	-
	Black Oxide STYS	16	200	90		55	18	M16		120	60	14	M12	7		-	-	-
	Trivalent Chromate STTS	12	150	100	9	75	16	M12	70	100	60	14	M12	7	50	-	-	-

Ordering Example
Part Number: **STYS12**

Ribbed

STRS (Black)
STRZ (Silver)

STRW (Black)
STRZW (Silver)

Type	Material	Surface Treatment
STRS	S25C	Black Baked Finish
STRW		Black Baked Finish
STRZ		Baked Paint (Silver)
STRZW		Baked Paint (Silver)

RoHS 10

Part Number	Type	No.	H	L	C	T1	T2	T3	T4	W1	W2	D		B	F1	F2	G		d	P	ℓ	Y	E	Unit Price		
												Hole Dia.	Applicable Screw				Slotted Hole	Applicable Screw						STRS, STRW	STRZ, STRZW	
Single	Black STRS	8	125	50	40	6	10	4	5	30	23	12	M8	35	50	50	7	M6	7	-	115	20	12			
	Silver STRZ	10	160	60	45	8	12	5	5	35	27	14	M10	40	60	75	9	M8	9	-	150	25	15			
	Black STRW	12	200	72	55	10	15	6	5	45	35	16	M12	50	70	100	11	M10	11	-	188	30	18			
Double	Black STRW	10	150	60	-	8	12	5	10	65	8	14	M10	40	50	60	9	M8	9	30	140	25	15			
	Silver STRZW	12	200	80	-	10	15	6	15	80	10	16	M12	60	70	100	11	M10	11	50	188	30	20			

Ordering Example
Part Number: **STRS12**