

Hinge Bases

Center Fulcrum, 2 Point Mounting

Features: A dimension (lateral direction) has been minimized by placing a mounting hole in the center.

U-Shaped	T-Shaped	M Material	S Surface Treatment
HGCCJB	HGCCB	S45CEquivalent	Black Oxide
HGCCJM	HGCCM	SUS304	Electroless Nickel Plating
HGCCJS	HGCCS	SUS304	-

U-Shaped

T-Shaped

RoHS10

* For U-Shaped Type, when choosing W6 or Less, W tolerance is +0.05 ~ +0.2.

Part Number	A Selectable	W 1mm Increment	H 1mm Increment	C	F	B	S	T	d	Unit Price												
										U-Shaped			T-Shaped									
Type	DH7									HGCCJB	HGCCJM	HGCCJS	HGCCB	HGCCM	HGCCS							
U-Shaped HGCCJB HGCCJM HGCCJS	3	12	3~6	12~20	25	18	H+T/2	5	9	4.5												
	4	12																				
	5	19	5~11	14~25																		
		22	5~14																			
	6	19	5~11								32	25										
		22	5~14																			
T-Shaped HGCCB HGCCM HGCCS	8	19	6~11	17~25																		
	8	22	6~14																			
		22	10~12	17~30																		
	10	25	10~15	22~35	38	30																
		22	10~12																			
	12	25	10~15					8	19	5.5												
	13	25																				
	14	30																				
	15	30	12~20	26~40	50	40																
	16	30																				
20	38	15~25	28~45																			
25	38		36~50	65			50		15	30	9											



Ordering Example

Part Number - A - W - H
 HGCCJS12 - A22 - W10 - H30
 HGCCB10 - A25 - W12 - H20



Example

