

Phenol Pull Handles / Cantilever Pull Handles / Plastic Pull Handles with Caps

Outside Mount



Phenol Pull Handles

RoHS10

UPCFAN

Material

Phenol Resin

Part Number		L ₁	h	H	R	C	L _c	Mass (g)	Unit Price
Type	L								
UPCFAN	90	111	29	50	6.5	10.5	6.5	88	
	114	135						108	
	120	141						116	
	140	161	39	60	8.5	13.5	8.5	131	
	160	181						145	
	180	201						164	
	200	221						178	

Cantilever Pull Handles

RoHS10

Type	Handles		Cap
	Material	Surface Treatment	Material
HHKP	Glass Fiber Reinforced Nylon (Mat Black)	-	Nylon 6 (Mat Black)
HHKA	ADC12	Baked Paint (Silver)	Nylon 6 (Mat Gray)

ex Example

Hex Socket Head Cap Screw
Small Diameter Spring Washer

⚠ Screws and washers are not included.

Part Number	Type	H	h	A	R	C	L _r	L _c	D	P	K	Allowable Load (N)		Mass (g)		Unit Price	
												HHKP	HHKA	HHKP	HHKA	HHKP	HHKA
80	HHKP (Plastic)	29	18	16	3	6	5	3	24	12	6	60	200	15	28		
100	HHKA (Aluminum)	35	19	20	4	8	6	4	28	12	8	90	320	29	56		
147		50.5	30	29	6	11	9	6	38	19	9	150	500	78	170		

Plastic Pull Handles with Caps

UPCDG
(Nylon 6)

Material

Glass Fiber Reinforced Nylon 6

Part Number		L ₁	Allowable Load (N)	Mass (g)	Unit Price
Type	L				
UPCDG	90	133	500	30	
	94	136.5		33	
	117	160		36	
	132	175		39	

Ordering Example

Part Number
UPCFAN90
HHKP100
UPCDG132

Nuts for Pull Handles

RoHS10

HHPUW

Material: SUS304

Part Number	Type	P	Applicable Handle	Unit Price	Volume Discount Rate
HHPUW		90	UPCDG90	1 ~ 9 pc (s).	10~100

Ordering Example

Part Number
HHPUW90