


Air blow videos are now on the web! ▶ MISUMI Nozzles Videos Search <http://jp.misumi-ec.com/>




Features
 Blow Port width approx. two times as wide as Standard Type (AFTSP).
 ⚠ To prevent damage
 • Avoid excessive tightening of screw.
 • Avoid shocks to the screws.

Part Number		Orifice	Air Flow Rate NL/Min (for 0.3MPa)	Weight (g)	Unit Price 1 ~ 4 pc(s).	Volume Discount Rate		
Type	No.					5-39	40-99	100-200
AFTW	20	32-Ø1	290	40				

⚠ For orders larger than indicated quantity, please check with WOS.

Ordering Example Part Number
 AFTW20




Features
 More compact than Standard Type (AFTSP). (Width: Approx. 40%, Overall Length: Approx. 60% more compact)
 ⚠ To prevent damage
 • Avoid excessive tightening of screws.
 • Avoid shocks to the screws.

Part Number		Orifice	Air Flow Rate NL/Min (for 0.3MPa)	Weight (g)	Unit Price 1 ~ 4 pc(s).	Volume Discount Rate		
Type	No.					5-39	40-99	100-200
AFTC	7	22-Ø0.7	210	5				

⚠ For orders larger than indicated quantity, please check with WOS.

Ordering Example Part Number
 AFTC7







Features
 More compact than Standard Type (AFTSP). (Width: Approx. 40%, Overall Length: Approx. 60% more compact)
 ⚠ To prevent damage
 • Avoid excessive tightening of screws.
 • Avoid shocks to the screws.

Part Number		Orifice	Air Flow Rate NL/Min (for 0.3MPa)	Weight (g)	Unit Price 1 ~ 4 pc(s).	Volume Discount Rate		
Type	No.					5-9	10-19	20-30
AFTCA	7	5-Ø0.8, 6-Ø1.0	220	17				

⚠ For orders larger than indicated quantity, please check with WOS.

Ordering Example Part Number
 AFTCA7



⚠ Values on the graph are for reference, not guaranteed.