

# Hinge Bases


## Side Mounting T-Shaped

■ Features: T-Shaped Side Mounting Type.



H Configurable		M Material	S Surface Treatment	A Accessory
H7 Type	H7 Type with Tap			
HKSBB	HKSBBT	S45C Equivalent	Black Oxide	Set Screws
HKSBS	-	SUS304	-	1 pc. (SUS304)

25 / ( / 6.3 / 1.6 / )



RoHS 10

⚠ For H7 Type, M part doesn't have tap and set screw. ⚠ Holes for D=2 are through holes, not counterbored.

■ H Configurable

Part Number Type	D <sub>H7</sub>	H 1mm Increment	W	A	F	B	K	T	d	d <sub>1</sub>	H <sub>1</sub>	M	Unit Price		
													HKSBB	HKSBS	HKSBBT
(H7) HKSBB HKSBS	2	15~20	4	13	7	H+3	10	6	3.5	6.5	3.5	M3			-
	3	15~25	6	16	8	H+5		9							
	4	20~30	8	19	11	H+6	12	12	4.5	8	4.5	M4			
	5			25	16	H+8		16							
	6	25~35	10	32	20	H+10	14	19	5.5	9.5	5.5	M5			
	8			38	26								22		
	10	30~40	12	50	36	H+12	15	25	6.5	11	6.5	M6			
	12												30	38	30
	13												35	40	30
	14												40	42	30
15	35~45	16	65	47	H+14	18	25	9	14	9	M6				
16												45	49	30	
20												50	53	30	
25	40~50	20	65	47	H+17	18	30	9	14	9	M6				

⚠ For detailed dimensions of Hinge Pin, see P. 1-908.

Ordering Example: Part Number - H  
HKSBB6 - H30

ex Example

