

Links

3-Hole

■ **Features:** 3-Hole Dimension Selectable at 1 mm Increment.

Type	Material	Surface Treatment
LNFTB	S45C	Black Oxide
LNFTM	Equivalent	Electroless Nickel Plating
LNFTS	SUS304	-

• T Dimension Tolerance

T	5-16	19-22
	-0.3-0	-0.33-0

⚠ L ≥ S ⚠ When D ≥ P, W ≥ D + 4.
When P > D, W ≥ P + 4 is required.

25 / (√1.6 /)

RoHS10

Links - 3-Hole

Part Number	*DH7	PH7 1mm Increment	VH7 1mm Increment	L 1mm Increment	S 1mm Increment	*W 1mm Increment	T Selection	F	C
LNFTB LNFTM LNFTS	3	*3~20	3~20 V ≤ D	10~150 (L ≥ S)	10~150 (S ≤ L)	10~20	5 6	5	3
	4						5 6 9		
	5						5 6 9		
	6						5 6 9		
	8						5 6 9 10		
	10						5 6 9 10		
	12			20~200 (L ≥ S)	20~200 (S ≤ L)	10~30	9 10 12 16	10	5
	13						9 10 12 16		
	14						9 10 12 16		
	15						9 10 12 16		
	16						9 10 12 16		
	18						9 10 12 16		
20	30~200 (L ≥ S)	30~200 (S ≤ L)	25~50	9 10 12 16 19	15	8			
25				30~60			9 10 12 16 19 22	18	

*When D ≥ P, W ≥ D + 4; when P > D, W ≥ P + 4 is required.

Ordering Example **Part Number** - P - V - L - S - W - T
LNFTB10 - P8 - V10 - L100 - S50 - W20 - T9



Alterations



Part Number - P - V - L - S - W - T - (TPD, TPP, TPV)
LNFTB20 - P18 - V18 - L50 - S30 - W40 - T16 - TPD

DH7	Unit Price (L ≥ S)								
	LNFTB			LNFTM			LNFTS		
	Min. L - 50	L51-150	L151 - Max. L	Min. L - 50	L51-150	L151 - Max. L	Min. L - 50	L51-150	L151 - Max. L
3									
4									
5									
6									
8									
10									
12									
13									
14									
15									
16									
18									
20									
25									

Alterations

Code **TPD, TPP, TPV**

Spec. Adds tapped holes at D, P and V.
 Applicable Dimensions

D/P/V	W	Tightening Screw M (Included)
12	24~30	M4
13	25~30	
14	26~40	
15	27~40	
16	28~40	
18	36~40	
20	38~50	M5
25	43~60	