


Circular Plates

Standard Grade / Precision Grade




RoHS 10

Standard Grade

Type		Material
Standard	Configurable Size	
ENPMH	ENPM	(Steel) SS400
ENPNH	ENPN	(Aluminum) A5052P-H112
ENPDH	ENPD	(Duralmin) A2017P-T351
ENPGH	ENPG	(Stainless Steel) SUS303

⚠ Circumference Chamfering C0.5 or Less




⚠ Parallelism of any 1,000mm is 2mm based on the material accuracy.

Precision Grade

Type		Material
Standard	Configurable Size	
ENPSH	ENPS	(Steel) SS400
ENPAH	ENPA	(Aluminum) A5052P-H112
ENPJH	ENPJ	(Duralmin) A2017P-T351
ENPUH	ENPU	(Stainless Steel) SUS303

⚠ Circumference Chamfering C0.5 or Less



⚠ Parallelism of any 100mm is the value of B.

Standard Grade, Standard Size

Part Number	Type	T	D Selection	d 1mm Increment	T Dimension Tolerance	Unit Price			
						D100	D150	D200	D300
ENPMH (SS400)	10	15	100	0~50	±0.6				
			150						
ENPNH (A5052P)	10	15	100	0~50	±0.6				
			150						
ENPDH (A2017P)	10	15	100	0~50	±0.6				
			150						
ENPGH (SUS303)	10	15	100	0~50	±0.6				
			150						

Precision Grade, Standard Size

Part Number	Type	T	D Selection	d 1mm Increment	B Parallelism	Unit Price			
						D100	D150	D200	D300
ENPSH (SS400)	10	15	100	0~50	0.012				
			150						
ENPAH (A5052P)	10	15	100	0~50	0.03				
			150						
ENPJH (A2017P)	10	15	100	0~50	0.03				
			150						
ENPUH (SUS303)	10	15	100	0~50	0.03				
			150						

Standard Grade, Configurable Size

Part Number	Type	T	D	d 1mm Increment	T Dimension Tolerance	Unit Price							
						D50	D201	D301	D401	D501	D601	D701	
ENPM (SS400)	10	15	8-9	50-200	0-50	±0.2							
			10	50-600									
			11-15										
			16-20										
			21-25										
ENPN (A5052P)	10	15	8-9	50-200	0-50	±0.2							
			10			±0.6							
			11-14			±0.2							
			15			±0.7							
			16-19			±0.2							
ENPD (A2017P)	10	15	8-9	50-200	0-50	±0.2							
			10			±0.6							
			11-14			±0.2							
			15			±0.7							
			16-19			±0.2							
ENPG (SUS303)	10	15	8-9	50-200	0-50	±0.2							
			10			±0.6							
			11-15			±0.2							
			16-20			±0.7							
			21-25			±0.2							

Precision Grade, Configurable Size

Part Number	Type	T	D	d 1mm Increment	B Parallelism	Unit Price							
						D50	D201	D301	D401	D501	D601	D701	
ENPS (SS400)	10	15	8-9	50-200	0-50	0.012							
			10	50-600	0-100								
			11-15										
			16-20										
			21-25										
ENPA (A5052P)	10	15	8-9	50-200	0-50	0.03							
			10			0.05							
			11-14			0.07							
			15			0.09							
			16-19			0.11							
ENPJ (A2017P)	10	15	8-9	50-200	0-50	0.03							
			10			0.05							
			11-14			0.07							
			15			0.09							
			16-19			0.11							
ENPU (SUS303)	10	15	8-9	50-200	0-50	0.03							
			10			0.05							
			11-15			0.07							
			16-20			0.09							
			21-25			0.11							

Ordering Example: Part Number - D - d
 ENPNH15 - 200 - 8
 ENPN19 - 670 - 18