
New NICECUT



Body

φD

φD1

		F:-	Blades	Dimensions (mm)										۰	luut-		
	Model No.			φD	φD1	φDb	φd	L	ls	₽n	₽b	S	(g) (α°	Inserts	base	arm
NS	NKN20-100S-03	0	3	100	112	78	20	123.5	80	43.5	120	5.0	1,525	45	S32MOZ / S32GUR		AMNS-03
	NKN32-100S-03	0	3	100	112	78	32	123.5	80	43.5	120	5.0	1,825	45	S32MOZ / S32GUR	NK32078-03	AMNS-03
	NKN20-130S-03	0	3	130	142	108	20	123.5	80	43.5	120	5.0	2,755	45	S32MOZ / S32GUR		AMNS-03
	NKN32-130S-03	0	3	130	142	108	32	123.5	80	43.5	120	5.0	3,055	45	S32MOZ / S32GUR	NK32108-03	AMNS-03
	NKN32-150S-03	0	3	150	162.5	128	32	120	85	35	116.5	5.0	2,505	45	S32MOZ / S32GUR	NK32128-03	AMNS-03
	NKN32-100S-06	0	6	100	112	78	32	123.5	80	43.5	120	5.0	1,890	45	S32MOZ / S32GUR	NK32078-06	AMNS-06
	NKN32-130S-06	0	6	130	142	108	32	123.5	80	43.5	120	5.0	3,120	45	S32MOZ / S32GUR	NK32108-06	AMNS-06
PS	NKP32-100S-03	8	3	100	115	78	32	123.5	80	43.5	120	6.2	1,834	45	S3H3MNZ / S3H3GNZ	NK32078-03	AMPS-03
	NKP32-130S-03	2	3	130	145	108	32	123.5	80	43.5	120	6.2	3,064	45	S3H3MNZ / S3H3GNZ	NK32108-03	AMPS-03
	NKP32-150S-03	9	3	150	164.7	128	32	120	85	35	116.5	6.2	2,514	45	S3H3MNZ / S3H3GNZ	NK32128-03	AMPS-03
	NKP32-100S-06	8	6	100	115	78	32	123.5	80	43.5	120	6.2	1,908	45	S3H3MNZ / S3H3GNZ	NK32078-06	AMPS-06
	NKP32-130S-06	9	6	130	145	108	32	123.5	80	43.5	120	6.2	3,138	45	S3H3MNZ / S3H3GNZ	NK32108-06	AMPS-06
NT	NKN32-110T-03	8	3	110		78	32	123.5	80	43.5	120	14.5	1,849	90	T33MOZ / T33MOR / T33GUR	NK32078-03	AMNT-03
	NKN32-140T-03	3	3	140		108	32	123.5	80	43.5	120	14.5	3,079	90	T33MOZ / T33MOR / T33GUR	NK32108-03	AMNT-03
	NKN32-160T-03	3	3	160		128	32	120	85	35	116.5	14.5	2,529	90	T33MOZ / T33MOR / T33GUR	NK32128-03	AMNT-03
	NKN32-110T-06	8	6	110] \	78	32	123.5	80	43.5	120	14.5	1,938	90	T33MOZ / T33MOR / T33GUR	NK32078-06	AMNT-06
	NKN32-140T-06	3	6	140] \	108	32	123.5	80	43.5	120	14.5	3,168	90	T33MOZ / T33MOR / T33GUR	NK32108-06	AMNT-06

φD

 ϕ D1

^{*} Clamp screw, lock pin, cap screw and wrench are supplied as standard accessories



When mounting or replacing insert, please do not take reverse tightening.

Due to the eccentricity looking mechanism, poor accuracy or breakage of insert may be occurred by reverse tightening

φD

^{*} Insert is not equipped as standard accessories. Please order separately